


- Heatsinks f.cool
- Cases f.case
- Connectors f.con
 - Sockets
 - PCB connectors
 - Male headers
 - Female headers
 - Direct female connector
 - Jumpers
 - IDC-connectors
 - D-Sub connectors
 - Brackets for PC
 - Optoelectronics

Female headers

BL 1 14 G

Stamped contact spring (fork contact), for 0.635 mm
V-notches permit breaking! Therefore any required number of contacts is available.

add to request



Features	Technical Drawing	Accessories / related products
no. of contacts		14
contact material		CuSn-Legierung
surface contact / contact sleeve		Ni+0,2µm Au Ni+4...6µm Sn
surface of contact		gold-plated
Typ Innenfeder		Gabelkontakt
plugability		0,5 mm bis 0,7 mm
insertion depth		1,5 ... 5,0 mm
plug-in cross-section		square 0.635
insertion / extraction force		1,5 N / 1,3 N
volume resistivity		≤10 mΩ
capacity between two adjacent contacts		≤ 0,9 pF
nominal current		3 A
nominal voltage		125 V AC
test voltage		1500 V
material isolation body		PPS
temperature range		-40 °C ... +163 °C (260 °C / 10 s)
class of flammability		UL 94 V-0
insulation resistance		>10 ¹² Ω
version		stamped contact spring (fork contact)
connection type		soldering
reflow solderable		yes