




C1

C2

Part-No. / 产 品 号 码	Length/长度
33 15 243 050 0003 .00	500±5
33 15 243 020 0002 .00	200±3
33 15 243 010 0001 .00	100±3

NOTES/要求:

- 1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST AND HI-POT (300VDC) TEST.
- 2.) CABLE OPERATION TEMPERATURE= -30° C TO +105° C .
- 3.) WHITE LABEL CONTENT:

DATE CODE & LOT INFORMATION
HARTING P/N & REVISION

01	Add side view.	Lucy.Z	15/04/13
00	Prototype	Andrew.H	24/05/11
Rev.	Description	Appr.	Date

 All Dimensions in mm Original Size DIN A4				Ref. MB	
Free size tol.				Mat.	
V=	cm ³	A=	cm ²	SEE BILL OF MATERIAL	
	Name	Date	Scale	Title	
	Detail		✓	Har-Flex female 6pole, double ended	
	Insp.		Sheet	Flat cable assembly, L=xMM	
	Approved		1 of 1		

HARTING (Zhuhai) Manufacturing Co., Ltd.					
			DWG. No. TB_33 15 0001 .01		