

# PRINTED CIRCUIT TRANSFORMERS

## Plug-In Printed Circuit Series




\* Agency Certification Note: UL Recognized (File E68100)


All Single Primaries are 115V 50/60Hz, 6 Pins

All Dual Primaries are 115/230V 50/60Hz, 8 Pins

PC Type




APC Type




RoHS

| Sec. | STANCOR<br>PART | Style | Primary<br>Winding | VA   | Rated Output |                     |      |                 |      |                   | DIMENSIONS - INCHES |      |      |      |      |   |      | Weight<br>(lbs.) | Agency<br>Certif. |                                                                                       |
|------|-----------------|-------|--------------------|------|--------------|---------------------|------|-----------------|------|-------------------|---------------------|------|------|------|------|---|------|------------------|-------------------|---------------------------------------------------------------------------------------|
|      | NUMBER          |       |                    |      | AC/DC        | Individual<br>Volts | mA   | Series<br>Volts | mA   | Parallel<br>Volts | mA                  | H    | W    | L    | ML   | A | B    |                  |                   | C                                                                                     |
| A    | PPC-1           | PC    | Single             | 1.5  | AC           | 4.0                 | 188  | 8.0 C.T.        | 188  | 4.0               | 376                 | 1.19 | 1.41 | 1.16 | -    | - | 0.31 | 1.00             | 0.22              |    |
|      | PPC-2           | PC    | Single             | 1.5  | AC           | 7.5                 | 100  | 15.0 C.T.       | 100  | 7.5               | 200                 | 1.19 | 1.41 | 1.16 | -    | - | 0.31 | 1.00             | 0.22              |    |
|      | PPC-46          | PC    | Dual               | 1.5  | AC           | 7.5                 | 100  | 15.0 C.T.       | 100  | 7.5               | 200                 | 1.19 | 1.41 | 1.16 | -    | - | 0.20 | 1.00             | 0.22              |    |
|      | PPC-3           | PC    | Single             | 1.5  | AC           | 15.0                | 50   | 30.0 C.T.       | 50   | 15.0              | 100                 | 1.19 | 1.41 | 1.16 | -    | - | 0.31 | 1.00             | 0.22              |    |
|      | PPC-8           | PC    | Dual               | 1.5  | AC           | 15.0                | 50   | 30.0 C.T.       | 50   | 15.0              | 100                 | 1.19 | 1.41 | 1.16 | -    | - | 0.20 | 1.00             | 0.22              |    |
| B    | PPC-18          | APC   | Dual               | 4.5  | AC           | 6.3                 | 350  | 12.6 C.T.       | 350  | 6.3               | 700                 | 1.44 | 2.38 | 1.25 | 2.00 | - | 0.25 | 1.10             | 0.47              |    |
|      | PPC-19          | APC   | Dual               | 4.5  | AC           | 8.0                 | 280  | 16.0 C.T.       | 280  | 8.0               | 560                 | 1.44 | 2.38 | 1.25 | 2.00 | - | 0.25 | 1.10             | 0.47              |    |
| C    | PPC-20          | APC   | Dual               | 4.5  | AC           | 12.0                | 180  | 24.0 C.T.       | 180  | 12.0              | 360                 | 1.44 | 2.38 | 1.25 | 2.00 | - | 0.25 | 1.10             | 0.47              |    |
|      | PPC-17          | APC   | Single             | 4.5  | AC           | 20.0                | 112  | 40.0 C.T.       | 112  | 20.0              | 224                 | 1.44 | 2.38 | 1.25 | 2.00 | - | 0.40 | 1.10             | 0.47              |   |
|      | PPC-14          | APC   | Single             | 4.5  | AC           | 27.0                | 84   | 54.0 C.T.       | 84   | 27.0              | 168                 | 1.44 | 2.38 | 1.25 | 2.00 | - | 0.40 | 1.10             | 0.47              |  |
| D    | PPC-23          | APC   | Single             | 7.5  | AC           | 15.0                | 250  | 30.0 C.T.       | 250  | 15.0              | 500                 | 1.63 | 2.81 | 1.47 | 2.38 | - | 0.40 | 1.30             | 0.66              |  |
|      | PPC-58          | PC    | Dual               | 24.0 | AC           | 12.0                | 1000 | 24.0 C.T.       | 1000 | 12.0              | 2000                | 1.44 | 1.63 | 2.31 | -    | - | 0.25 | 2.11             | 0.90              |  |


PC Style (Single)




PC Style (Dual)




APC Style (Single)



APC Style (Dual)



Single Input



Dual Input

