


Type F Vertical Receptacle Assemblies with Wrap Type and Solder Posts



Material

Housing — Glass filled polymer

Contacts — Copper alloy

Related Product Data

DIN Performance Levels —Page 6

Performance Specifications —

Page 8

Mateable Connectors — Pages 36,

39

PC Board Hole Layout — Page 61


Accessories — Page 68, 69

Technical Documents — Page 74:

DIN Specification 41612


IEC Specification 60603-2

Instruction Sheet 408-6784



Number of Positions	Post Type	Rows Loaded	DIN Level	Part Number
48	Wrap Type 1.00 [.039] Square	Z,B,D	II	166717-4
	4.00 [.157] Solder	Z,B,D	II	166733-4
32	Wrap Type 1.00 [.039] Square	Z,D	II	166719-4
	4.00 [.157] Solder	Z,D	II	166951-4

Recommended Panel Cutout



Post Type	Post Dimensions		
	A	B	C
Wrap Type	1.00	1.00	22.00
1.00 [.039] Square	.039	.039	.866
4.00 [.157] Solder	0.60	0.30	4.00
	.022	.012	.157