



**Project:** fghjkl  
**Location:** sdfghbn

**werftghb**  
**wefhtrsjednuky6jsg**

## Russellstoll®

**J-Line Interconnection Systems**

**T&B Catalog Number:**

**UPC Number:**

JRS1044FR

**Status:**

70891718443

**Description:**

Active

J-Line Basic Reverse Service Receptacle Watertight (Screw Cover), 100 Amp, 4 Pole 4 , with 1.5" Bushing I.D.

### Features

One-piece interior assemblies interchangeable from regular to reverse service in the field with a screw-driver. Reversed contacts flexibility within any housing.

Wiring space ample for maximum requirements; cable clamps are adjustable for maximum range of cable sizes.

Quick conversion between weathertight flap cover and watertight screw cap assemblies. Flap cover can be rotated and locked in any convenient position.

Quick conversion between weathertight flap cover and watertight screw cap assemblies. Flap cover can be rotated and locked in any convenient position.

### Application

Value alternative to MaxGard® in 3 Pole 4 Wire, 30 to 200 Amp applications with less severe need.

Value alternative to MaxGard in 3 Pole 4 Wire, 30 to 200 Amp applications with less severe need.

### General

|            |  |
|------------|--|
| Style      | Reverse Service Basic Receptacle   |
| Material   | Cast aluminum, corrosion-resistant copper-free alloy housings and enclosures |
| Material_1 | Epoxy powder coat finish   |
| Material_2 | Silver plated contacts   |
| Frequency  | 60 Hz  |
| Amperage   | 100 Amp  |
| Pole/Wire  | 4P/4W  |
| System     | Heavy Industrial & Marine  |

### Dimension Information

Overall Dimensions Available on Website

### Specifications

|         |                       |
|---------|-----------------------|
| Voltage | Maximum 600VAC/250VDC |
|---------|-----------------------|

**Packaging**

|                    |               |
|--------------------|---------------|
| Package in Units   | 1             |
| T&B Sold in UOM    | Each          |
| T&B Weight Per UOM | 3.4 lbs. Each |

**Application Support**

|                                |                      |
|--------------------------------|----------------------|
| Overview                       | Available on Website |
| Russellstoll Application Guide | Available on Website |

**Certifications**

|                 |    |
|-----------------|----|
| RoHS Compliance | No |
|-----------------|----|

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)