

4




3

2

1

used for:

D-SUB



Directive 2002/95/EC
"RoHS"
Compliant

POS.	A±0.2	B±0.3	C±0.15	D-0.2	E+0.2	F±0.1	Part-no.
9	37.60	34.30	25.00	20.50	14.40	11.40	799-102080
15	45.90	42.50	33.30	28.80	14.40	11.40	799-101180
25	59.60	56.40	47.00	42.50	14.40	11.40	799-101780
37	76.10	72.70	63.50	59.10	14.40	11.40	799-101980
50	73.70	70.70	61.10	56.30	17.10	14.10	799-101880


2	Spring steel bow	2	Stainless steel no. 1.4571
1	Base element	1	Stainless steel no. 1.4541 / 1.4571
quantity	part description	Item	material

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish:
black plating
method Deltasil

tolerance
ISO 7168-m



scale: 2:1

material:

title:

Base element
with spring steel bow
design D-SUB

dwg no:

AutoCAD 2000

DIN-A

7992A001A

4

sh: 1/1

part no:

SEE TABLE

CONEC®

1 x b	Ä2675	26.02.2007	E.Mick.
"a"	Ä 1236	20.02.2001	Parei
rev.	description	date	name

4

3

2

1