

Thrust ball bearings, single direction



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Minimum load factor A	Speed ratings		Mass	Designation
d	D	H	dynamic	static			Reference speed	Limiting speed		
mm			kN	C ₀	kN	-	r/min		kg	-
50	78	22	49,4	116	4,3	0,069	3400	4500	0,37	51210

