




THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.
© 2003, Projects Unlimited Inc.

SPECIFICATIONS

PARAMETERS	VALUES	UNITS
RATED INPUT POWER	0.3	W
MAX INPUT POWER	0.5	W
IMPEDANCE	8±15%	OHM
OUTPUT SPL @ 0.3W/10CM (AT 1.0, 1.2, 1.5, 2.0 kHz)	86±3	dBA
DISTORTION	5%	—
RESONANT FREQUENCY	850±20%	Hz
FREQUENCY RANGE	850 ~ 20,000	Hz
HOUSING MATERIAL	PPS	—
CONE MATERIAL	POLYESTER	—
MAGNET MATERIAL	SmCo	—
OPERATING TEMPERATURE	-40 ~ +85	°C
WEIGHT	2.1	grams



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. SPECIFICATION SUBJECT TO CHANGE OR WITHDRAWAL WITHOUT NOTICE.

FILE NAME
SMS-1508.DWG

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
—	RELEASED FROM ENGINEERING	7/30/03	
A	REVISED TO NEW TEMPLATE	6/9/04	R. W.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN
MILLIMETERS, TOLERANCES ARE ±0.5 AND
ANGLES ARE ±3°.



projects®
unlimited

Dayton , Ohio

SURFACE MOUNT SPEAKER
SMS-1508

APPROVALS DATE

DRAWN T. P. I. 7/03

APPROVED S. J. 7/03

DO NOT SCALE DRAWING

SIZE
A

DRAWING NO.
SMS-1508

SCALE: N.T.S.

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[PUI Audio:](#)

[SMS-1508](#)