




SF 4240	Rated Current A	Leakage Current @ 250V 50Hz	Inductance mH L1 L2 L3			Connections	Resistor Value MΩ	Approvals		
SF 4240-1/01	1	0.2mA	4.3	4.3	0.3	6.3 x 0.8 Faston	1			
SF 4240-3/01	3	0.2mA	2.2	2.2	0.3	6.3 x 0.8 Faston	1			
SF 4240-6/01	6	0.2mA	1.3	1.3	0.3	6.3 x 0.8 Faston	1			
SF 4240-10/01	10	0.2mA	1.0	1.0	0.3	6.3 x 0.8 Faston	1			
SF 4240-16/01	16	0.2mA	0.45	0.45	0.3	6.3 x 0.8 Faston	1			


Temperature Range: -25°C to +85°C
Operating Voltage: 440/250Vac
Operating Frequency: 0 to 400Hz
Test Voltage: L+N to ground, 2700Vdc, 2 seconds

☒ Approved
☐ Submitted for Approval

DIMENSIONS

All dimensions are nominal and in mm

IEC 950 (EN 60950 Applications)



CIRCUIT DIAGRAM

