










Specifications

- **Certifications*:** UL, CSA
- **Dielectric Strength:** 1,000V (minimum)
- **Insulation Resistance:** 100 Megohms (minimum)
- **Base Material:** Phenolic
- **Actuator Material:** Brass/Nickel Plate
- **Bushing Material:** Brass/Nickel Plate

Dimensional Specifications: in. [mm]



 .125[3.18] DIA .330[8.38] .187[4.74] SOLDER LUG	 .075[1.91] DIA .437[11.09] .250[6.35] .250 TAB (Q.C.)	 .055[1.40] DIA .394[10.00] .187[4.74] .187 TAB (Q.C.)
TERMINAL TYPE		
 #6-32NC-2 THREAD .141[3.58] .370[9.39] .286[7.26] SCREW (ASSEMBLED)	 6.000[152.40] .500[12.70] WIRE LEAD	
 .062[1.57] MOUNTING HOLE	 .038[9.65] .500[12.70] DIA WITH KEYWAY	 .376[9.55] .500[12.70] DIA .125[3.17] DIA WITH LOCKING RING

2F A 5 3 - 73 /TABS

SERIES	RATING ¹	TERMINATION/FUNCTION ²			
2F SINGLE POLE	5 10A 250VAC		SOLDER	.250TAB	SCREW
6F SINGLE POLE	15A 125VAC	FUNCTION	LUG	(QC)	TERM.
MOMENTARY	3/4HP 120-240VAC	ON-NONE-OFF	3	3/TABS	4
		(ON)-NONE-OFF	3	3/TABS	4
	6 3A 250VAC	ON-NONE-(OFF)	7	7/TABS	8
	6A 125VAC	ON-NONE-ON	3	3/TABS	4
	1/4HP 120-240VAC	ON-NONE-(ON)	3	3/TABS	4
		ON-OFF-ON	3	3/TABS	4
		(ON)-OFF-(ON)	3	3/TABS	4
		ON-OFF-(ON)	7	7/TABS	8
					6
A ON-NONE-OFF					
B ON-NONE-ON					
C ON-OFF-ON					

	TOGGLE LENGTH	BUSHING LENGTH	SUFFIX NO.	NEOPRENE SEAL
BAT	.406	.343	52	57
	.562	.465	63	68
	.687	.465	73	78
	1.00	.343	A2	A7
	2.00	.465	E3	E8
BALL	.500	.343	22	---

Add the suffix /.187TABS. (ex.) 2FA53-73/.187TABS