








SOLDERING SIDE
LOETSEITE

[illegible]

MATERIAL / MATERIAL: PBT, UL-94 V2 SHELL MATERIAL / GEAHÄUSEMATERIAL: CUZN FINISH / BESCHICHTUNG: TRIBOR 4 µm	
WIRE GAGE / DRAHTGROESSE IN mm ² : 0.25	
WIRE GAGE / DRAHTGROESSE IN mm ² : 0.14	
CONTACT RESISTANCE / KONTAKTWIDERSTAND: >= 5 mΩ	
RATED CURRENT PER CONTACT / NENNSTROM PRO KONTAKT: 3 A	
RATED CURRENT PER CONTACT / NENNSTROM PRO KONTAKT: 1 A	
SHELL PROTECTION CLASS / SCHUTZKLASSE: IP 65 / DIN 40050	
TERMINATION: SOLDERING / VERBINDUNG: LOETKONTAKTE	
TEST VOLTAGE / PRUEFSPANNUNG: 500 VAC	
OPERATING VOLTAGE / BETRIEBSSPANNUNG: 60 VAC	
OPERATING TEMPERATURE: -40°C TO +80°C / ARBEITSTEMPERATUR: -40°C BIS +80°C	
MATING CYCLES / STECKZYKLEN: 500 MAX.	
TECHNICAL DATA TECHNISCHE DATEN	

TYCO NO. / TYCO-NR.						
4-1437719-2	3-1437719-9	3-1437719-6	3-1437719-3	3-1437719-0		
1	1	1	1	1	MOUNTING WRENCH / MONTAGESCHLUESSEL	19
1	1	1	1	1	SEALING PAD / GUMMIDICHTUNG	18
1	1	1	1	1	COMPLETELY IN MINI-GRIP / KOMPLETT IN MINI-GRIP-BEUTEL: 70x100mm)	17
1	1	1	1	1	MOUNTING INSTRUCTION / MONTAGEANLEITUNG	16
1	1	1	1	1	INSULATION TUBE / ISOLIERHUELSE	15
1	1	1	1	1	SCREWING TUBE / SCHRAUBHUELSE	14
1	1	1	1	1	SPRING / FEDER	13
1	1	1	1	1	TUBE / INNENHUELSE	12
1	1	1	1	1	O-RING / O-RING	11
1					CONTACT CARRIER 8 WAY/BUCHSENSTECKER 8 POLIG	10
	1				CONTACT CARRIER 7 WAY/BUCHSENSTECKER 7 POLIG	9
		1			CONTACT CARRIER 5 WAY/BUCHSENSTECKER 5 POLIG	8
			1		CONTACT CARRIER 4 WAY/BUCHSENSTECKER 4 POLIG	7
				1	CONTACT CARRIER 3 WAY/BUCHSENSTECKER 3 POLIG	6
1	1	1	1	1	GROUNDING PLATE FOR 360°SHIELDING CONNECTION/ MASSESCHIEBE FUER 360°ABSCHIRMUNG	5
1	1	1	1	1	HOUSING / GEHAUESE	4
1	1	1	1	1	CABLE SEALING / KABELDICHTUNG	3
1	1	1	1	1	STRAIN RELIEF / ZUGENTLASTUNGSKRONE	2
1	1	1	1	1	STRAIN RELIEF NUT / ZUGENTLASTUNGSMUTTER	1
-	-	-	-	-	REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG REV.)	
QTY REQD PER ASSY						
T01-0550-S08	T01-0550-S07	T01-0550-S05	T01-0550-S04	T01-0550-S03	DESCRIPTION BESCHREIBUNG	ITEM NO POS.-NR.
					PARTS LIST TEILELISTE	
CATALOG-N0.	CATALOG-N0.	CATALOG-N0.	CATALOG-N0.	CATALOG-N0.		

[illegible]