


151-2P14-E, 151-2P16-E, 151-2P24-E



IDC DIP Flat Cable Plugs

151-2P14-E, 151-2P16-E, 151-2P24-E

DIMENSIONS: mm



RECOMMENDED P.C.B LAYOUT

ELECTRICAL SPECIFICATIONS

Current Rating:	1 Amp
Contact Resistance:	30mΩ max.
Insulation Resistance:	3000MΩ min.
Dielectric Withstanding Voltage:	Voltage: 500V AC for 1 minute
Operating Temperature:	-40°C to +105°C

MATERIAL

Insulator:	1 Amp
Contact:	Phosphor Bronze

Date Last Revised: 10-05-10

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301391

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[151-2P24-E](#) [151-2P16-E](#) [151-2P14-E](#)