




REVISIONS					
ZONE	LTR	DESCRIPTION		DATE	APPROVED
	A	REDRAWN & UPDATED	PC-5561	10-15-69	<i>[Signature]</i>
	B	BUTT WAS PARALLEL	PC-5575	5-8-70	<i>[Signature]</i>
	B1	REV PER ECR 05-013140		10/20/05	<i>[Signature]</i>



BUSHING

SLEEVE ASSEMBLY

WIRE SPLICE

FOR .064 TO .088 WIRE INSULATION DIA.

2	BUSHING	21428-1	TEFLON (ASTM D3295) COLOR: NATURAL
1	WIRE SPLICE	328592	COPPER (QQ-C-576) GOLD PL (MIL-G-45204) TYPE II .00005 MIN THK OVER NICKEL PL (QQ-N-290) .00003 MIN THK
1	SLEEVE ASSY	328798	INSULATION: TEFLON (ASTM D3295) COLOR: NAT. RING: ALUMINUM (QQ-A-250/1) COLOR: RED
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS ±.008 ANGLES ± 5° MATERIAL SEE TABLE		CONTRACT NO.	AMP INCORPORATED HARRISBURG, PENNSYLVANIA
		DR. <i>[Signature]</i> 10-3-69	NAME WIRE SPLICE POST INSULATED STRATO-THERM MOISTURE SEAL-BUTT WIRE SIZE: 18-16
		CHK <i>[Signature]</i> 10-15-69	
		APPD <i>[Signature]</i> 10-20-69	
		REL <i>[Signature]</i> 10-20-69	
		DSGN APPD	SIZE B CODE IDENT NO. 00779 NUMBER 329647
		OTHER APPD	SCALE NT5 SHEET 1 OF 1