



A254

AC/DC Amp Low Current Probe Adapter



Measurement Range

AC Amps: 10mA to 40A

DC Amps: 10mA to 60A

Accuracy

$\pm (1.5\% + 20\text{mA})$
basic accuracy

Adapter Output

10mV per 1A or
100mV per 1A

General Specifications

Maximum Conductor Size: 0.35" (9mm)

Lead Length: 48" (1.2m)

Output Connection Type: BNC connector with removable banana plug adapter

Use This Adapter With

Most TPI brand and any competitor DMM, clamp-on or oscilloscope having the capability of measuring up to 2000mV AC/DC (2V AC/DC), 10M Ohm input impedance, and equipped with industry standard spaced input jacks 19mm on center.

Copyright © 2007 Test Products International, Inc.