




Home / Products / Hose & Tubing / Ribbon Hose / URH8-0804-02T-050

Knowledge Base

- [Clippard's Automated Pneumatic Stamping Machine](#)
 - [Pneumatic Solutions for Oxygen Concentration](#)
 - [Modular Circuit Assembly Tips](#)
 - [Pneumatic Solutions for Leak Testing](#)
 - [Clippard Value-Added Services](#)
 - [Why Choose Quick-Connect Fittings?](#)
- [more...](#)



URH8-0804-02T-050

Type

85A Polyurethane Hose 8-Ribbon

Outer Diameter (Inner Diameter)

1/4" (1/8")

Length

50 feet

(In Stock)

Qty:

1

Add to Cart

Details

Polyurethane Ribbon Hose, 1/4" OD-1/8" ID, Multi-Color, 50' Roll

Notes

In normal application hose clamps are not required with hose when used with Clippard hose barb fittings
See Catalog: [Page 331](#)

Uses

Ideal for feeding supply in on one line and out on the other; reduces labor; makes neat assembly; may be parted with any sharp cutting edge

Additional Information

Accessories	Clamp 5000-1
Bend Radius	3/8"
Color	Ribbon of White, Gray, Purple, Blue, Green, Yellow, Orange, Red
Inner Diameter	1/8"
Length	50 feet
Outer Diameter	1/4"
Outer Diameter (Inner Diameter)	1/4" (1/8")
Static Burst Pressure	Over 500 psig at 70°F
Type	85A Polyurethane Hose 8-Ribbon
Working Range	0 to 105 psig at 100°F Maximum 120°F



Company History
Our Credo
Community
ISO 9001:2008
Warranty
Privacy Notice
Job Opportunities

Products

[Catalog Home](#)
[Search the Catalog](#)
[Request Literature](#)
[Monthly E-Newsletter](#)

Distributors

[Find a Distributor](#)
[Technical Help](#)
[Trade Show Schedule](#)

Application Ideas

[Product How to's](#)
[Product Tips](#)
[Installation Instructions](#)
[Applications](#)

Downloads

[Full Line Catalog](#)
[Product Brochures](#)
[Training PDFs](#)
[Product Data Bulletins](#)

Toll Free 877.245.6247