

**Specifications:**

|                              |                                                                                                  |
|------------------------------|--------------------------------------------------------------------------------------------------|
| <b>Sound Level Category</b>  | Medium                                                                                           |
| <b>Mode of Operation</b>     | Continuous tone                                                                                  |
| <b>Voltage Rating</b>        | 16 to 28 VAC/DC                                                                                  |
| <b>Frequency</b>             | 2900 Hz $\pm$ 500 Hz                                                                             |
| <b>Loudness @ 2 FT</b>       | 75 to 85 dB(A) typ. (16 to 28 VAC/DC)                                                            |
| <b>Current Draw</b>          | 20 mA Max (16 to 28 VAC/DC)                                                                      |
| <b>Housing Material</b>      | Nylon 6/6 (Color: Black)                                                                         |
| <b>Storage Temperature</b>   | -40°C to +85°C                                                                                   |
| <b>Operating Temperature</b> | -30°C to +65°C                                                                                   |
| <b>Panel Mounting</b>        | Recommended hole size is 1.25in (31.75mm). Threaded front will fit standard 30mm (1.181in) hole. |
| <b>Knurled Nut</b>           | Used to attach part to panel. The max recommended torque is 10 in-lbs                            |
| <b>Termination</b>           | 5mm standard socket used with pluggable screw terminal block.                                    |
| <b>Weight (Typical)</b>      | 1.05 oz (30 g)                                                                                   |
| <b>NEMA 3R, 4X, &amp; 12</b> | Approved with use of ACC03.                                                                      |
| <b>Options</b>               | For other options contact factory                                                                |

**Dimensions:** Inches (mm)**RoHS Compliant**