




WIRE-WOUND COMMON MODE CHOKE CHIP INDUCTORS-0805 Series(2012) (67~180Ω)

Part Number	Impedance (Ω) @100MHZ	Percent Tolerance	R _{DC} Max Ohms	Rated Voltage Vdc(V)max	Rated current Max mA
ACMC0805-670MFS	67	20	0.35	50	330
ACMC0805-900MFS	90	20	0.35	50	330
ACMC0805-121MFS	120	20	0.45	50	280
ACMC0805-151MFS	150	20	0.50	50	250
ACMC0805-181MFS	180	20	0.50	50	250

Working Temperature Range : -40 °C ~ 85 °C

Shape & Dimension




	A		B		C		E	F	G	H	I	J	K
	Max.	Ref	Max	Ref	Max	Ref							
inch	0.087	0.079	0.055	0.047	0.043	0.039	0.016	0.047	0.016	0.015	0.030	0.043	0.020
mm	2.20	2.00	1.65	1.40	1.10	1.00	0.40	1.20	0.40	0.38	0.75	1.10	0.50

Parts/Reel: 7" 3,000 pcs

Tape Width: 8mm

EQUIVALENT CIRCUIT



TYPICAL ELECTRICAL CHARACTERISTIC CURVES

Impedance & Frequency

