



SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PX00LF	D09S91C6PX00LF	D09S91C8PX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PX00LF	D15S91C6PX00LF	D15S91C8PX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PX00LF	D25S91C6PX00LF	D25S91C8PX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PX00LF	D37S91C6PX00LF	D37S91C8PX00LF
						gold flash	0.76µ gold	1.25µ gold

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	MASSON	2000/07/27	ANGULAR	LINEAR	0.X		±0.1		size A3	Scale 2
Eng	PESSON	2000/07/27			0.XX		±0.1			
Chr	LEGARE	2000/07/27			0.XXX		±0.1			
Appr	LEGARE	2000/07/27	0.XX ±2°				ECN		LS06-0140	
			Product family				D-SUB		Spec ref -	
			title FEMALE CONNECTOR DELTA D STRAIGHT PRESS-FIT				dwg no C01-8646-0129		Rev. H	
catalog no										

rev	ecn no	dr	date
E	-	MAS	2000/07/27
F	LS05-004	MPE	2005/02/08
G	LS06-0097	LGO	2006/07/29
H	LS06-0140	LGO	2006/09/22
-	-	-	-
-	-	-	-
-	-	-	-