


Nylon Insulated Banana Jacks


For standard 0.175" banana plug. Formed brass contact, bright-tinned finish. Comes with nickel-plated nut. **Panel Thickness:** to 0.343". **Current:** 15 A. **Contact Resistance:** 0.010 ohms.



| Stock No. | Mfr.'s Type  | Color  | EACH |       |         |
|-----------|--------------|--------|------|-------|---------|
|           |              |        | 1-24 | 25-99 | 100-999 |
| 528-0157  | 108-0901-001 | White  | .48  | .39   | .32     |
| 528-0158  | 108-0902-001 | Red    | .48  | .39   | .32     |
| 528-0159  | 108-0903-001 | Black  | .48  | .39   | .32     |
| 528-0160  | 108-0904-001 | Green  | .48  | .39   | .32     |
| 528-0161  | 108-0906-001 | Orange | .48  | .39   | .32     |
| 528-0162  | 108-0907-001 | Yellow | .48  | .39   | .32     |
| 528-0163  | 108-0908-001 | Brown  | .48  | .39   | .32     |
| 528-0164  | 108-0910-001 | Blue   | .48  | .39   | .32     |
| 528-0165  | 108-0912-001 | Violet | .48  | .39   | .32     |
| 528-0166  | 108-0913-001 | Gray   | .48  | .39   | .32     |

Insulated Metal-Clad — Military Type Tip Jacks

For 0.080" diameter standard tip plug. Comes with nylon body and nickel-plated brass jacket. Gold-plated turret terminal contact with wrap-around beryllium copper spring. Come with nickel-plated washer and nut. Mounts in panels 0.218" thick. **Breakdown Voltage:** 5700 Vrms. **Current:** 10 A. Conform with MS-16108, Rev. F of MIL-STD-242A and MIL-C-39024/10.



| Stock No. | Mfr.'s Type  | Color  | EACH |       |         |
|-----------|--------------|--------|------|-------|---------|
|           |              |        | 1-24 | 25-99 | 100-999 |
| 528-0107  | 105-0201-200 | White  | 2.25 | 1.83  | 1.51    |
| 528-0108  | 105-0202-200 | Red    | 2.25 | 1.83  | 1.51    |
| 528-0109  | 105-0203-200 | Black  | 2.25 | 1.83  | 1.51    |
| 528-0110  | 105-0204-200 | Green  | 2.25 | 1.83  | 1.51    |
| 528-0111  | 105-0207-200 | Yellow | 2.25 | 1.83  | 1.51    |
| 528-0112  | 105-0210-200 | Blue   | 2.25 | 1.83  | 1.51    |

Insulated Metal-Clad Standard Tip Jacks

For 0.080" diameter standard tip plug. Nylon body and nickel-plated threaded, brass jacket. Silver-plated contact is phosphor bronze with slotted terminal. Comes with nickel-plated nut. Mount panels to 0.281" thick. **Breakdown Voltage:** 5700 Vrms minimum. **Current:** 10 A.



| Stock No. | Mfr.'s Type  | Color | EACH |       |         |
|-----------|--------------|-------|------|-------|---------|
|           |              |       | 1-24 | 25-99 | 100-999 |
| 528-0184  | 105-0251-001 | White | .95  | .77   | .64     |
| 528-0185  | 105-0252-001 | Red   | .95  | .77   | .64     |
| 528-0186  | 105-0253-001 | Black | .95  | .77   | .64     |

Vertical Test Jacks



Mounts through 0.052" hole and requires minimum mounting area. Accepts 0.080" dia. tip plugs. Silver-plated machined or formed beryllium copper contacts. 5 amps.

Machined Contacts

| Stock No. | Mfr.'s Type  | Color | EACH |       |         |
|-----------|--------------|-------|------|-------|---------|
|           |              |       | 1-24 | 25-99 | 100-999 |
| 528-0213  | 105-0851-001 | White | .55  | .45   | .37     |
| 528-0214  | 105-0852-001 | Red   | .55  | .45   | .37     |
| 528-0215  | 105-0853-001 | Black | .55  | .45   | .37     |

Formed Contacts

|          |              |       |     |     |     |
|----------|--------------|-------|-----|-----|-----|
| 528-0219 | 105-2201-201 | White | .49 | .40 | .33 |
| 528-0220 | 105-2202-201 | Red   | .49 | .40 | .33 |
| 528-0221 | 105-2203-201 | Black | .49 | .40 | .33 |

Rib-Loc® Tip Jacks

Accept standard 0.080" diameter tip plugs. Simply press into mounting hole. Silver-plated terminals. **Current:** 5 A. **Breakdown Voltage:** 3500 Vrms. **Contact Resistance:** 0.005 ohm max.



| Stock No. | Mfr.'s Type  | Color | EACH |       |         |
|-----------|--------------|-------|------|-------|---------|
|           |              |       | 1-24 | 25-99 | 100-999 |
| 528-0208  | 105-1041-001 | White | 1.02 | .83   | .69     |
| 528-0209  | 105-1042-001 | Red   | 1.02 | .83   | .69     |
| 528-0210  | 105-1043-001 | Black | 1.02 | .83   | .69     |


Insulated Solderless Banana Plugs



For standard 0.166" banana jack. Tapered insulated nylon handle. Connect with wire up to 16 gauge. Nickel-plated brass body with nickel silver plug spring. **Current:** 15 A. **Contact Resistance:** 0.010 ohms.

| Stock No. | Mfr.'s Type  | Color  | EACH |       |         |
|-----------|--------------|--------|------|-------|---------|
|           |              |        | 1-24 | 25-99 | 100-999 |
| 528-0147  | 108-0301-001 | White  | 1.00 | .81   | .67     |
| 528-0302  | 108-0302-001 | Red    | 1.00 | .81   | .67     |
| 528-0149  | 108-0303-001 | Black  | 1.00 | .81   | .67     |
| 528-0304  | 108-0304-001 | Green  | 1.00 | .81   | .67     |
| 528-0306  | 108-0306-001 | Orange | 1.00 | .81   | .67     |
| 528-0152  | 108-0307-001 | Yellow | 1.00 | .81   | .67     |
| 528-0310  | 108-0310-001 | Blue   | 1.00 | .81   | .67     |
| 528-0155  | 108-0312-001 | Violet | 1.00 | .81   | .67     |
| 528-0156  | 108-0313-001 | Gray   | 1.00 | .81   | .67     |

Insulated Banana Plugs — Hex Body, Solder Stud



For standard banana jacks of 0.166" ID. Wire can be soldered to threaded-stud or flared and held by stud for solderless connection. Accept up to 16-gauge wire. Nylon insulated handle is UL approved for self extinguishing. Plug is nickel-plated brass with nickel silver spring. **Current Rating:** 15 amps. **Breakdown Voltage:** 3500 Vrms minimum. **Contact Resistance:** 0.010 ohms maximum.

| Stock No. | Mfr.'s Type  | Color | EACH |       |         |
|-----------|--------------|-------|------|-------|---------|
|           |              |       | 1-24 | 25-99 | 100-999 |
| 528-0197  | 108-1762-101 | Red   | 1.68 | 1.37  | 1.13    |
| 528-0198  | 108-1763-101 | Black | 1.68 | 1.37  | 1.13    |


Insulated Standard Tip Jacks



For standard 0.080" diameter tip plug. Nylon body, phosphor bronze contact, tin plated. **Panel Thickness:** 0.437" max. **Current:** 10 A. **Breakdown Voltage:** 5700 Vrms minimum.

| Stock No. | Mfr.'s Type  | Color  | EACH |       |         |
|-----------|--------------|--------|------|-------|---------|
|           |              |        | 1-24 | 25-99 | 100-999 |
| 528-0174  | 105-0801-001 | White  | .61  | .50   | .41     |
| 528-0175  | 105-0802-001 | Red    | .61  | .50   | .41     |
| 528-0176  | 105-0803-001 | Black  | .61  | .50   | .41     |
| 528-0179  | 105-0807-001 | Yellow | .61  | .50   | .41     |
| 528-0181  | 105-0810-001 | Blue   | .61  | .50   | .41     |

Insulated Stacking Dual Banana Plugs (Set Screw)



Molded body incorporates polarity indication and stain relief for wire leads. **Voltage Breakdown:** 3500 Vrms. **Capacity Plug to Plug:** 1.3 pf. **Current** 10 A. **Breakdown Voltage:** 3500 Vrms.

| Stock No. | Mfr.'s Type  | Color | EACH |       |         |
|-----------|--------------|-------|------|-------|---------|
|           |              |       | 1-24 | 25-99 | 100-999 |
| 528-0225  | 108-0252-001 | Red   | 5.03 | 4.16  | 3.30    |
| 528-0226  | 108-0253-001 | Black | 5.03 | 4.16  | 3.30    |

Insulated Standard Binding Posts


For standard 0.175" diameter banana plug. Flatted, insulated nylon body prevents turning. Silver-plated brass stud has turret termination. Comes with nickel-plated nut. **Current:** 15 A. **Breakdown Voltage:** 5700 Vrms minimum. **Panel Thickness:** 0.261" max.



| Stock No. | Mfr.'s Type  | Color  | EACH |       |        |
|-----------|--------------|--------|------|-------|--------|
|           |              |        | 1-9  | 10-49 | 50-249 |
| 528-0137  | 111-0101-001 | White  | 1.82 | 1.48  | 1.23   |
| 528-0138  | 111-0102-001 | Red    | 1.82 | 1.48  | 1.23   |
| 528-0139  | 111-0103-001 | Black  | 1.82 | 1.48  | 1.23   |
| 528-0140  | 111-0104-001 | Green  | 1.82 | 1.48  | 1.23   |
| 528-0141  | 111-0106-001 | Orange | 1.82 | 1.48  | 1.23   |
| 528-0142  | 111-0107-001 | Yellow | 1.82 | 1.48  | 1.23   |
| 528-0143  | 111-0108-001 | Brown  | 1.82 | 1.48  | 1.23   |
| 528-0144  | 111-0110-001 | Blue   | 1.82 | 1.48  | 1.23   |
| 528-0145  | 111-0112-001 | Violet | 1.82 | 1.48  | 1.23   |
| 528-0146  | 111-0113-001 | Gray   | 1.82 | 1.48  | 1.23   |


Insulated Deluxe Tip Jacks

For 0.080" diameter standard tip plug. Machined silver-plated brass contact with turret terminal and wrap-around beryllium copper spring. Comes with threaded nylon body and nickel-plated nut. Mount in panels to 0.437" thick. **Current:** 10 A. **Breakdown Voltage:** 5700 Vrms minimum.



| Stock No. | Mfr.'s Type  | Color  | EACH |       |         |
|-----------|--------------|--------|------|-------|---------|
|           |              |        | 1-24 | 25-99 | 100-999 |
| 528-0117  | 105-0601-001 | White  | 1.07 | .87   | .72     |
| 528-0118  | 105-0602-001 | Red    | 1.07 | .87   | .72     |
| 528-0119  | 105-0603-001 | Black  | 1.07 | .87   | .72     |
| 528-0120  | 105-0604-001 | Green  | 1.07 | .87   | .72     |
| 528-0122  | 105-0607-001 | Yellow | 1.07 | .87   | .72     |
| 528-0124  | 105-0610-001 | Blue   | 1.07 | .87   | .72     |

Insulated Tip Jacks with Sleeve Assembly



For standard 0.080" diameter tip plug. Machined, silver-plated brass contact with turret terminal and wrap-around beryllium copper spring. Assembled body and handle are nylon. For panel thicknesses to 0.125"; 10 A. **Contact Resistance:** 0.010 ohms.

| Stock No. | Mfr.'s Type  | Color | EACH |       |         |
|-----------|--------------|-------|------|-------|---------|
|           |              |       | 1-24 | 25-99 | 100-999 |
| 528-0101  | 105-0701-001 | White | 1.35 | 1.10  | .91     |
| 528-0102  | 105-0702-001 | Red   | 1.35 | 1.10  | .91     |
| 528-0103  | 105-0703-001 | Black | 1.35 | 1.10  | .91     |


Insulated Solderless Tip Plugs

For 0.080" diameter standard tip jacks. Nylon insulating handle with nickel-plated brass plug contact. Accept wire sizes to 16 gauge. Head recessed to reduce shock hazard. **Current:** 10 A. **Breakdown Voltage:** 3500 Vrms.



| Stock No. | Mfr.'s Type  | Color | EACH |       |         |
|-----------|--------------|-------|------|-------|---------|
|           |              |       | 1-24 | 25-99 | 100-999 |
| 528-0127  | 105-0301-001 | White | .74  | .60   | .49     |
| 528-0128  | 105-0302-001 | Red   | .74  | .60   | .49     |
| 528-0129  | 105-0303-001 | Black | .74  | .60   | .49     |
| 528-0130  | 105-0304-001 | Green | .74  | .60   | .49     |

Panel Mount Uninsulated Banana Plugs and Jacks



Brass body per QQ-B-626D. Plugs have nickel silver springs per QQ-C-585. **Screw Type Plugs (Fig. 1):** 108-0753, for standard jack; 0.125" panel thickness, 14 gauge wire; 15 A. 108-0771, jumbo plug, panel thickness 0.093" to 0.500"; 12 gauge; 40 A. **Jacks Have Nickel Finish (Fig. 2):** Type 108-0740, 0.375" panel thickness; 12 gauge wire; 15 A; pierced lug.

| Stock No. | Mfr.'s Type  | Fig. | Description           | EACH |       |         |
|-----------|--------------|------|-----------------------|------|-------|---------|
|           |              |      |                       | 1-24 | 25-99 | 100-999 |
| 528-0169  | 108-0753-001 | 1    | Plug, 6-32 screw      | 1.08 | .88   | .73     |
| 528-0171  | 108-0771-001 | 1    | Jumbo plug with screw | 2.89 | 2.36  | 1.86    |
| 528-0172  | 108-0740-001 | 2    | Standard jack         | 1.17 | .96   | .79     |