





General ordering data

Order No.	9508010000
Part designation	NexT 98/74/20 8gp 7032
Version	Ex enclosure, 205 mm, 980 mm, 740 mm, Sheet steel 2.02 mm (14 SWG)
EAN	4008190499594
Qty.	1 pc(s).

Dimensions

Fixing dimension, height	700 mm
Fixing dimension, width	796 mm
Height	205 mm
Length	980 mm
Width	740 mm

General details

Cover fixing	Removable cover + M6 screws
Enclosure fixing	Outside mounting with 10 mm holes
Integral fixing	4 x 10 mm spacers
Sealing material	Chloroprene (cover & flange)
Version cover	closed
Colour	RAL 7032 - pebble grey
Surface finish	RAL 7032, textured
Class of protection to EN 60529	IP 66
Weight	38,000 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	85 °C

Screwed cable glands top/bottom

M 12	162
M 16	120
M 20	76
M 25	48
M 32	24
M 40	20

Screwed cable glands top/bottom


M 50	8
M 63	6
M 75	4
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M12	222
M16	160
M20	104
M25	60
M32	32
M40	24
M50	10
M63	8
M75	4
On housing side	left / right

Approvals

Approvals institutes

**Classifications**

ETIM 2.0	EC000049
ETIM 3.0	EC000049
eClass 4.1	27-14-12-06
eClass 5.0	27-18-05-02
eClass 5.1	27-18-05-02

Similar products

Order No.	Part designation	Version
9523720000	NexT 98/74/20 0gp 7032	Ex enclosure, 205 mm, 980 mm, 740 mm, Sheet steel 2.02 mm (14 SWG)
9523020000	NexT 98/74/20 2gp 7032	Ex enclosure, 205 mm, 980 mm, 740 mm, Sheet steel 2.02 mm (14 SWG)
9522740000	NexT 98/74/20 2gp ss	Ex enclosure, 205 mm, 980 mm, 740 mm, Stainless steel 1.4404
9507940000	NexT 98/74/20 4gp 7032	Ex enclosure, 205 mm, 980 mm, 740 mm, Sheet steel 2.02 mm (14 SWG)
9508750000	NexT 98/74/20 4gp ss	Ex enclosure, 205 mm, 980 mm, 740 mm, Stainless steel 1.4404
9523160000	NexT 98/74/20 6gp 7032	Ex enclosure, 205 mm, 980 mm, 740 mm, Sheet steel 2.02 mm (14 SWG)
9522880000	NexT 98/74/20 6gp ss	Ex enclosure, 205 mm, 980 mm, 740 mm, Stainless steel 1.4404

9508820000	NexT 98/74/20 8gp ss	Ex enclosure, 205 mm, 980 mm, 740 mm, Stainless steel 1.4404
------------	----------------------	--