

HC-B 6-TFL-40/M1PG13,5G

Order No.: 1771121



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1771121>

Sleeve housing, for single locking latch, height 40 mm, with screw connection, 1x Pg13.5, straight cable entry

Commercial data

GTIN (EAN)	4 017918 035860
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 480 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B6, BB10, DD24, M
Design	B6
Height	40 mm
Width	43 mm
Length	60 mm

Housing type	Sleeve housings
Locking type	for single locking latch
Cable exit	Straight
Type of the screw connection	1x Pg13,5
Pg screw connection	With
Wrench size, union nut	20 mm
External cable diameter	7.5 mm ... 12.5 mm
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR

Certificates / Approvals




Certification

GOST

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;