


A		B		C		D		E		F		G		H	
DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED										
XX4-32X-D		X1	CUSTOMER APPROVAL	03/26/99	E.V.										
		X2	ADD RETRACTED LENGTH	03/29/99	E.V.										

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. UNLESS OTHERWISE NOTED, ALL DIMENSIONS ARE IN INCHES (MILLIMETER). THIS DRAWING IS THE PROPERTY OF I/O INTERCONNECT INC. AND IS NOT TO BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS APPLICABLE SUBSIDIARIES.



OPEN END

PI



CUSTOMER APPROVAL
ENGR. SIGN *Matt Slemmer*
DATE: 4-13-99

NOTES: UNLESS OTHERWISE SPECIFIED.

1. TEST CABLE FOR ALL OPENS & SHORTS.
2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.


TABULATION BLOCK

IOI PART NUMBER	IOI CABLE PART NUMBER	EXTENDED LENGTH *X*	RETRACTED LENGTH *R*	COLOR
464-144-325-D	121-410-022	14.0 FT (4.3 M)	34.0 IN (863.6 MM)	WHITE
464-144-324-D	121-410-012	14.0 FT (4.3 M)	34.0 IN (863.6 MM)	BLACK
464-144-323-D	121-410-002	14.0 FT (4.3 M)	34.0 IN (863.6 MM)	SILVER SATIN
464-104-322-D	121-410-021	10.0 FT (3.0 M)	30.0 IN (762.0 MM)	WHITE
464-104-321-D	121-410-011	10.0 FT (3.0 M)	30.0 IN (762.0 MM)	BLACK
464-104-320-D	121-410-001	10.0 FT (3.0 M)	30.0 IN (762.0 MM)	SILVER SATIN
464-074-325-D	121-410-020	7.0 FT (2.1 M)	21.0 IN (533.4 MM)	WHITE
464-074-324-D	121-410-010	7.0 FT (2.1 M)	21.0 IN (533.4 MM)	BLACK
464-074-323-D	121-410-000	7.0 FT (2.1 M)	21.0 IN (533.4 MM)	SILVER SATIN
464-054-325-D	121-410-023	5.0 FT (1.5 M)	17.0 IN (431.8 MM)	WHITE
464-054-321-D	121-410-013	5.0 FT (1.5 M)	17.0 IN (431.8 MM)	BLACK
464-054-320-D	121-410-003	5.0 FT (1.5 M)	17.0 IN (431.8 MM)	SILVER SATIN

THIRD ANGLE PROJECTION		I/O INTERCONNECT		SANTA ANA, CALIFORNIA	
2	*X* FT	IOI	SEE "TABULATION BLOCK"	MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 4 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).	6P4C COIL CABLE TO OPEN END, CABLE ASSEMBLY
1	1 PC	IOI	325-641-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 4 CONDUCTOR, 50" AW, FLAT TYPE EXIT.	PART NO. 464-XX4-32X-D
ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION	REV.
					X1 X2
					REV. X2
					SCALE NONE
					SHEET 1 OF 1

CABLE ASSEMBLY PARTS LIST

A		B		C		D		E		F		G		H									
DRAWING SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S.A. THIS SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.												DWG. NO. XX4-50X-D		ZONE X1		REV. X1		DESCRIPTION CUSTOMER APPROVAL		DATE 03/25/99		APPROVED E.V.	
												ADD RETRACTED LENGTH		03/29/99		E.V.							





CUSTOMER APPROVAL
ENGR. SIGN Math Danner
DATE: 4-13-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. TEST CABLE FOR ALL OPENS & SHORTS.
 2. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

464-144-505-D	121-410-022	14.0 FT (4.3 M)	34.0 IN (863.6 MM)	WHITE
464-144-504-D	121-410-012	14.0 FT (4.3 M)	34.0 IN (863.6 MM)	BLACK
464-144-503-D	121-410-002	14.0 FT (4.3 M)	34.0 IN (863.6 MM)	SILVER SATIN
464-104-502-D	121-410-021	10.0 FT (3.0 M)	30.0 IN (762.0 MM)	WHITE
464-104-501-D	121-410-011	10.0 FT (3.0 M)	30.0 IN (762.0 MM)	BLACK
464-104-500-D	121-410-001	10.0 FT (3.0 M)	30.0 IN (762.0 MM)	SILVER SATIN
464-074-503-D	121-410-020	7.0 FT (2.1 M)	21.0 IN (533.4 MM)	WHITE
464-074-504-D	121-410-010	7.0 FT (2.1 M)	21.0 IN (533.4 MM)	BLACK
464-074-503-D	121-410-000	7.0 FT (2.1 M)	21.0 IN (533.4 MM)	SILVER SATIN
464-054-502-D	121-410-023	5.0 FT (1.5 M)	17.0 IN (431.8 MM)	WHITE
464-054-501-D	121-410-013	5.0 FT (1.5 M)	17.0 IN (431.8 MM)	BLACK
464-054-500-D	121-410-003	5.0 FT (1.5 M)	17.0 IN (431.8 MM)	SILVER SATIN
IOI PART NUMBER	IOI CABLE PART NUMBER	EXTENDED LENGTH "X"	RETRACTED LENGTH "R"	COLOR

THIRD ANGLE PROJECTION				I/O INTERCONNECT SANTA ANA, CALIFORNIA			
				UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN INCHES (MILLIMETER) 2) TOLERANCES: XXX ± 0.05 (6.35)			
MODULAR COIL CABLE, 26 AWG (7/34) BARE COPPER, 4 CONDUCTOR, UNSHIELDED, PVC JACKET, (SEE TABULATION BLOCK FOR COLOR).				REVERSE STYLE, CABLE ASSEMBLY			
CONNECTOR, MODULAR PLUG, 6 POSITION, 4 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.				PART NO. 464-XX4-50X-D			
DESCRIPTION				PART NO. 464-XX4-50X-D			
IOI PART NO.				CUSTOMER			
SCALE: NONE				SHEET 1 OF 1			

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC., U.S.A. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



WIRE DIAGRAM

P1	OPEN END
2	BLACK
3	RED
4	GREEN
5	YELLOW

CUSTOMER APPROVAL
 ENGR. SIGN Math Lerner
 DATE: 4-12-99

H3641-25-ND
 H3641-14-ND
 H3641-07-ND

464-254-522-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
464-144-522-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
464-074-522-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER	LENGTH *X*
I/O INTERCONNECT	

THIRD ANGLE PROJECTION

UNLESS OTHERWISE NOTED:
 1) DIMENSIONS ARE IN INCHES (MILLIMETER)
 2) TOLERANCES:
 XXX ± 0.025 (6.35)

SANTA ANA, CALIFORNIA	
PART NO. 464-XX4-522-D REV. NO. 464-XX4-522-D CUSTOMER DIGI KEY	SCALE: NONE SHEET 1 OF 1



- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	*X*	IOI	120-410-020	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 4 CONDUCTOR, UNSHIELDED, WHITE PVC.
1	1 PC	IOI	325-641-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 4 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST

A		B	C	D	E	F	G	H
DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED			
XX4-521-D		X1	CUSTOMER APPROVAL	03/24/99	E.V.			

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.



WIRE DIAGRAM

P1	OPEN END
2	BLACK
3	RED
4	GREEN
5	YELLOW

CUSTOMER APPROVAL
ENGR. SIGN Matt Arnes
DATE: 4-12-99

H3642-25-ND
H3642-14-ND
H3642-07-ND

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

464-254-521-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
464-144-521-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
464-074-521-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM


PART NUMBER
I/O INTERCONNECT
LENGTH "X"

THIRD ANGLE PROJECTION		I/O INTERCONNECT SANTA ANA, CALIFORNIA	
TITLE: 6P4C MODULAR TO OPEN END, BLACK, CABLE ASSEMBLY		PART NO: 464-XX4-521-D	
UNLESS OTHERWISE NOTED: 1) DIMENSIONS ARE IN INCHES (MILLIMETER) 2) TOLERANCES: X.XX ± 0.25 (6.35)		REV. X1	
DATE/FILED		CUSTOMER DIGI KEY	
SCALE: NONE		SHEET 1 OF 1	

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	X	IOI	120-410-010	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 4 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	1 PC	IOI	325-641-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 4 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.
CABLE ASSEMBLY PARTS LIST				


CABLE ASSEMBLY PARTS LIST

A	B	C	D	E	F	G	H
THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. ALL RIGHTS ARE RESERVED. NO PART OF THIS DOCUMENT IS TO BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.					DWG. NO. XX4-S11-D	REV. X1	DATE 03/24/99
					ZONE	CUSTOMER APPROVAL	APPROVED E.V.




WIRE DIAGRAM

P1	P2
2	BLACK
3	RED
4	GREEN
5	YELLOW



P2



CUSTOMER APPROVAL
ENGR. SIGN Math Jones
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE TO BE BUNDLED AND TWIST TIED.
 2. TEST CABLE FOR ALL OPENS & SHORTS.
 3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H1642 ~ 25' ND	464-254-S11-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
H1642 ~ 14' ND	464-144-S11-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
H1642 ~ 27' ND	464-074-S11-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM

PART NUMBER	LENGTH "X"
-------------	------------

THIRD ANGLE PROJECTION


I/O INTERCONNECT
SANTA ANA, CALIFORNIA

UNLESS OTHERWISE NOTED 1) DIMENSIONS ARE IN INCHES (MILLIMETER) 2) TOLERANCES XXX ± 0.25 (6.35)	REV. X1
DIGI KEY	REV. X1
SCALE NONE	SHEET 1 OF 1

ITEM	QTY	WFG.	DESCRIPTION
2	2 PCS	IDI	MODULAR CABLE, 26 AWG (7/34) BARE COPPER, 4 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	1	IDI	CONNECTOR, MODULAR PLUG, 6 POSITION, 4 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.
1	1	IDI	CONNECTOR, MODULAR PLUG, 6 POSITION, 4 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST

A	B	C	D	E	F	G	H
THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. NO PARTS OR INFORMATION HEREON ARE TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT PERMISSION IN WRITING FROM I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.	DWG. NO. XX4-502-D	REV. X1	DESCRIPTION CUSTOMER APPROVAL	DATE 03/24/99	APPROVED E.V.		



WIRE DIAGRAM

P1	P2
2	BLACK
3	RED
4	GREEN
5	YELLOW

CUSTOMER APPROVAL
 ENGR. SIGN Matt Lerner
 DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
1. CABLE TO BE BUNDLED AND TWIST TIED.
 2. TEST CABLE FOR ALL OPENS & SHORTS.
 3. PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

464-254-502-D	25.0 FT ± 4.0 IN 7.62 M ± 101.6 MM
464-144-502-D	14.0 FT ± 3.0 IN 4.27 M ± 76.2 MM
464-074-502-D	7.0 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER I/O INTERCONNECT	LENGTH "X"


I/O INTERCONNECT SANTA ANA, CALIFORNIA	
THIRD ANGLE PROJECTION 	TITLE 6P4C MODULAR, REVERT STYLE, WHITE, CABLE ASSEMBLY
UNLESS OTHERWISE NOTED 1) DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) TOLERANCES: XXX ± 0.25 (6.35)	PART NO. 464-XX4-502-D DWG NO. 464-XX4-502-D CUSTOMER DIGI KEY REV. X1
SCALE NONE SHEET 1 OF 1	

ITEM	QTY	MFG.	I/OI PART NO.	DESCRIPTION
2				MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 4 CONDUCTOR, UNSHIELDED, WHITE PVC.
1	2 PCS	I/OI	325-641-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 4 CONDUCTOR, 50u" Au, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST

THESE DRAWINGS AND SPECIFICATIONS ARE THE SOLE PROPERTY OF I/O INTERCONNECT INC. U.S. AND FOREIGN PATENTS AND TRADEMARKS ARE RESERVED. NO PART OF THIS DOCUMENT MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT WRITTEN CONSENT OF I/O INTERCONNECT INC. OR ITS AFFILIATED SUBSIDIARIES.

DWG. NO.	ZONE	REV.	DESCRIPTION	DATE	APPROVED
XX4-501-D		X1	CUSTOMER APPROVAL	03/24/99	E.V.



WIRE DIAGRAM


P1	P2
2	BLACK
3	RED
4	GREEN
5	YELLOW

CUSTOMER APPROVAL
ENGR. SIGN Math Jones
DATE: 4-12-99

- NOTES: UNLESS OTHERWISE SPECIFIED.
- CABLE TO BE BUNDLED AND TWIST TIED.
 - TEST CABLE FOR ALL OPENS & SHORTS.
 - PACKAGE CABLE ASSEMBLY INDIVIDUALLY IN PLASTIC BAG. PACKAGE INDIVIDUAL BAG PER LOT NUMBER QUANTITIES.

H2642-25-ND
H2642-14-ND
H2642-07-ND

464-254-501-D	250 FT ± 4.0 IN 7.62 M ± 101.6 MM
464-144-501-D	140 FT ± 3.0 IN 4.27 M ± 76.2 MM
464-074-501-D	70 FT ± 2.0 IN 2.13 M ± 50.8 MM
PART NUMBER I/O INTERCONNECT	LENGTH 'X'



TITLE	DATE	BY	CHKD	APP'D
I/O INTERCONNECT SANTA ANA, CALIFORNIA				

ITEM	QTY	MFG.	IOI PART NO.	DESCRIPTION
2	2 PCS	IOI	120-410-010	MODULAR CABLE, 26 AVG (7/34) BARE COPPER, 4 CONDUCTOR, UNSHIELDED, BLACK PVC.
1	2 PCS	IOI	325-641-50X	CONNECTOR, MODULAR PLUG, 6 POSITION, 4 CONDUCTOR, 50u" AU, FLAT TYPE EXIT.

CABLE ASSEMBLY PARTS LIST

REV.	DATE	BY	CHKD	APP'D
X1	03/24/99			
SCALE	NONE	SHEET	1	OF 1

