




PCB Phone Jack


161-3507

KOBI CONN



PCB Phone Jack



PCB Hole Layout (Bottom View)



Schematic



Dimensions: mm (in.)
Tolerance +/- 0.3mm(0.01)

SPECIFICATIONS	
Type:	Stereo, PCB mount
Insulation Resistance:	>100MΩ
Contact Resistance:	<10mΩ
Withstand Voltage:	250VAC for 1 minute
Soldering Temperature:	230±5°C for 5±.5 seconds
Bushing:	Nickel plated brass
Body:	Black plastic
Contact:	Silver plated phosphor bronze
Hardware Included:	Knurled nut
Mounting Holes:	.25"
	Can be water washed
	Wave solderable

Date Last Revised: 10-14-09

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300039

161-3507

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3507](#)