

SENSO-CASE

Order data on page 134

OKW
GEHÄUSE
SYSTEME




THE WAY AHEAD

Protection class IP 41

Max. size of PCB (L x W in inches)

top part	
M	2.913 x 2.913/1.063



THE PRODUCT

SENSO-CASE is ideal for ergonomically favourable single-handed operation, and offers many different possible applications.

Specific measuring, controlling and signalling tasks as well as the recording of data using opto-electronic components can be carried out easily, quickly and reliably.

Suitable for right handed and left handed operation.

YOUR ADVANTAGE

Ideal for pre-assembled electronics packages, including those with integrated interfaces.

Also available with push-button for immediate and/or temporary operation.

Internal power supply with 2 x 1.5 V mignon cells (AA) or 1 x 9 V flat battery (PP3). Battery compartment for 2 x AA as well as cable glands and a set of strain relief for cable operation available as accessories. Simultaneous operation using standard/rechargeable batteries and cable possible.



SENSO-CASE

Information on page 37

OKW
GEHÄUSE
SYSTEME



M

SENSO-CASE	Outside dim. in inches	L	L ₂	W	W ₂	H	H ₂
		7.067	3.071	3.386	1.260	1.772	0.984
		7.067	3.071	3.386	1.260	1.772	0.984

Equipment
push-button

–

• (single-pole)*¹

Material

ABS (UL 94 HB)

ABS (UL 94 HB)

Part-No.
off-white
RAL 9002

lava

A 90 56 107

A 90 56 207

A 90 56 108

A 90 56 208

SENSO-CASE ACCESSORIES

Article	For SENSO-CASE	Version / Application	Part-No.
① Battery holder* ²	M	PP, black, for 2 x 1.5 V mignon cells (AA), 1 pc	A 91 56 001
② Battery holder	M	spring steel, nickel-plated, for 1 x 9 V flat battery, 1 set	A 91 56 003
③ Plug-in contact* ³	M	for battery holder ① or 1 x 9 V flat battery, cable length 5.984"	A 91 56 002
④ Set of strain relief	M	for strain relief of cable connected applications	A 91 66 004
⑤ Cable gland	M	for cable ø 0.197" - 0.232", elastomer, volcano	A 91 66 101
		for cable ø 0.165" - 0.197", elastomer, volcano	A 91 66 131
		for cable ø 0.134" - 0.165", elastomer, volcano	A 91 66 161
⑥ Self-tapping screw	M	0.098" x 0.236", crosshead screw Z (PZ1), for mounting PCBs, 1 pc	A 03 05 031
⑦ Ring eyelet	M	plastic, volcano, inside ring ø 0.157", max. wall thickness 0.157", location hole ø 0.197" required	A 91 00 002

off-white lava

⑧ Holder	M	ABS, also suitable for cable connected applications	A 91 56 307	A 91 56 308
⑨ Adhesive foil	holder M	double-sided adhesive foil with foam carrier	A 91 56 005	



universal accessories on pages 178-187

*¹ case set incl. single-pole contact (max. 28 V/100 mA), assembly elements, connection cables and elastic cap made of TPE in the color orange; the protection class remains

*² contacts to fit the plug-in contact ③

*³ with protective case