



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'FZO12D5-5M15Y'

Your search criteria matched only one product, shown below

FZO12D5-5M15Y



- Pass all TIA/EIA-568-B.3 performance requirements
- FOCIS-5 compliant
- Insertion loss per mated pair: 0.50dB typical; 0.75dB max.
- Tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 550 meters at 850nm with 50/125µm (OM4) laser optimized fiber
- Backward compatible with all 50/125µm (OM2) MPO or MTP* system requirements
- Factory terminated and 100% tested for insertion loss
- Insertion loss and return loss data recorded for every 10Gig™ Multimode Interconnect Cable Assembly
- Lifetime traceability of test data to a Q.C. number on each cable assembly

Additional lengths and availability: Interconnect cable assemblies are available in 1 – 10 meter or feet lengths in 1 meter or foot increments, and 15, 20, 25 and 30 meter or feet lengths. To order lengths other than 1 meter or foot, replace the 1 after the M or F (FZ12D5-5M1 or FZ12D5-5F1) with the desired length (FZ12D5-5M2 or FZ12D5-5F2 for 2 meter or 2 feet length).

For other lengths or male MTPs*, contact Customer Service for actual lead times.

• Part Number	FZO12D5-5M15Y
• RoHS Compliancy Status	RoHS directive is not applicable
• Note	Intended for use in fixed installations which are outside the scope of RoHS
• Part Description	12 Fiber 10GIG OM4 Optimized Flat Ribbon Plenum Rated Female MTP - Female MTP Interconnect Cable Assemblies with .35dB IL - 15m
• Length (m)	15
• Fiber Compatibility	10 GbE 50/125µm
• Fiber Cable Type	Ribbon
• Fiber Type	Multimode
• Connector 1 Type	MTP* Connector
• Connector 2 Type	MTP* Connector
• End Configurations	MTP* to MTP*
• Fiber Count	12
• Flammability Rating	Plenum (OFNP)
• Pricing Description	MTP* to MTP* Optimized OM4 Interconnect Cable Assembly - 15m
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.