



SANDVIK BELZER

Nut drivers with handle

Material: blade of VANADIUM-EXTRA.

Ergonomically developed 3-component handle of polypropylene and thermoplastic elastomere.

Finish: blade fine polished and bright chrome plated, entirely hardened.

Permanent colour code on both ends of handle as time-saving aid for identification of the respective screw.




Long bore for projecting studs.

For male hexagon screws



Product code	EAN code 731415+		Dim mm	Bore depth mm				
					mm	mm	mm	g
BE-7803	1838867	5	3	40	125	20 x 122	247	70
BE-7835	1838874	5	3,5	40	125	20 x 122	247	70
BE-7804	1838881	5	4	50	125	20 x 122	247	70
BE-7845	1838898	5	4,5	50	125	20 x 122	247	70
BE-7805	1838904	5	5	50	125	20 x 122	247	72
BE-7855	1838911	5	5,5	50	125	20 x 122	247	72
BE-7806	1838928	5	6	50	125	20 x 122	247	85
BE-7807	1838935	5	7	50	125	27 x 122	247	85
BE-7808	1838942	5	8	50	125	27 x 122	247	90
BE-7809	1838959	5	9	50	125	36 x 122	247	95
BE-7810	1838966	5	10	50	125	36 x 122	247	117
BE-7811	1838973	5	11	50	125	36 x 122	247	140
BE-7812	1838980	5	12	50	125	36 x 122	247	145
BE-7813	1838997	5	13	50	125	36 x 161	286	145
BE-7814	1839000	5	14	50	125	36 x 161	286	213

With flexible blade.



BE-7606	1839017	5	6		150	27 x 122	272	85
BE-7607	1839024	5	7		150	27 x 122	272	85
BE-7608	1839031	5	8		150	27 x 122	272	95

IEC insulated nut drivers

For work on live equipment up to 1000 volts.

Conforms to IEC 900, EN 60900, DIN-EN 60900.

Examination of screwdrivers according to latest national and international standards:

- examination piece-wise in water bath with 10 KV
- marking with the year of manufacture
- intensified cold stroke test

Long bore for projecting studs.



BE-7855S	1839185	5	5,5	50	125	20 x 122	247	72
BE-7806S	1839192	5	6	50	125	20 x 122	247	85
BE-7807S	1839208	5	7	50	125	27 x 122	247	80
BE-7808S	1839215	5	8	50	125	27 x 122	247	90
BE-7809S	1839222	5	9	50	125	36 x 122	247	95
BE-7810S	1839239	5	10	50	125	36 x 122	247	117
BE-7811S	1839246	5	11	50	125	36 x 122	247	140
BE-7812S	1839253	5	12	50	125	36 x 122	247	145
BE-7813S	1839260	5	13	50	125	36 x 161	286	213