




REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
	V4	REVISED PER ECR-17-015029	11OCT2017	JB DZ


D





1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 – 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.

- △4 OPTIONAL FOR KEYING HOUSING IN PANEL.
- △5 CIRCUIT NUMBER 1 LOCATION.
- 6 DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- △7 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- △8 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.

C




DETAIL A
OPTIONAL CONSTRUCTIONS



RECOMMENDED PANEL CUT OUT

B



3-DIMENSIONAL MODEL
NTS

4.45	.175	27.43	1.080
2.79	.110	27.05	1.065
2.54	.100	26.67	1.050
2.41	.095	13.46	.530
2.29	.090	13.21	.520
0.76	.030	8.64	.340
0.38	.015	8.13	.320
0.25	.010	7.62	.300
0.13	.005	6.35	.250
MM	IN	MM	IN
CONVERSION TABLE			

CUSTOMER RESTRICTED	NATURAL	350780-2
	BLACK	1-350780-9
	GRAY	1-350780-8
	BLUE	1-350780-6
	GREEN	1-350780-5
	YELLOW	1-350780-4
	ORANGE	1-350780-3
	RED	1-350780-2
	BROWN	1-350780-1
NATURAL		350780-1
COLOR		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 15JUL92	 TE Connectivity	
DIMENSIONS: mm		CHK R. SWING 15JUL92	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. SELF 20JUL92	CAP.4 CIRCUIT, UNIVERSAL MATE-N-LOK™ —	
	0 PLC ± —	PRODUCT SPEC	SIZE CASE CODE DRAWING NO RESTRICTED TO	
	1 PLC ± —	—		
	2 PLC ± 0.13	APPLICATION SPEC		
	3 PLC ± —			
	4 PLC ± —			
ANGLES ± 1°		WEIGHT 0.000000		A1 00779 C=350780
FINISH —		CUSTOMER DRAWING		
MATERIAL NYLON,UL 94V-0		SCALE 4:1 SHEET 1 of 1 REV V4		