

4




3

2

1

used for:

D-SUB



(b)

Cable clamp has to be ordered separatly.  
Part-no. 16N61032

| POS. | A    | B    | C    | D    | ØE   | Part-NO. |
|------|------|------|------|------|------|----------|
| 9    | 31.0 | 25.0 | 35.5 | 14.8 | 12.1 | 16N61001 |
| 15   | 39.3 | 33.3 | 35.5 | 14.8 | 12.1 |          |
| 25   | 53.2 | 47.0 | 40.0 | 14.8 | 12.1 | 16N61002 |
| 37   | 69.5 | 63.5 | 40.0 | 14.8 | 12.1 |          |
| 50   | 67.0 | 61.1 | 42.0 | 17.8 | 14.6 |          |


**Delivery includes:**

Hood with covers  
1 or 2 blanking plugs  
4 screws for fixing  
1 earth screw  
2 jack screws

Directive 2002/95/EC  
RoHS  
Compliant

|                                                           |        |
|-----------------------------------------------------------|--------|
| APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL |        |
| CUSTOMER APPROVAL DATE:                                   |        |
| NAME:                                                     | TITLE: |
| COMPANY NAME:                                             |        |
| APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL |        |

THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH  
DO NOT ALTER CAD DRAWING BY HAND

|       |             |          |      |                                                                                     |        |                                                                                                   |
|-------|-------------|----------|------|-------------------------------------------------------------------------------------|--------|---------------------------------------------------------------------------------------------------|
|       |             |          |      | tolerance                                                                           |        | <br>dim. in mm |
|       |             |          |      | 2005                                                                                | date   | name                                                                                              |
|       |             |          |      | drawn                                                                               | 09.06. | Lehmenkühler                                                                                      |
|       |             |          |      | appd.                                                                               | 09.06. | Mickenbecker                                                                                      |
|       |             |          |      | norm                                                                                |        |                                                                                                   |
|       |             |          |      | d-old                                                                               |        |                                                                                                   |
| 1 x b | Ä 2459      | 13.03.06 | HS   |  |        |                                                                                                   |
| rev.  | description | date     | name |                                                                                     |        |                                                                                                   |

|           |                                                                     |         |
|-----------|---------------------------------------------------------------------|---------|
| scale:    | 1:1                                                                 |         |
| material: | DIE-CAST ZINC                                                       |         |
| title:    | <b>METAL HOOD</b><br>EMI/RFI shielding<br>9-50pos. with jack screws |         |
| dwg no:   | AutoCAD 2004                                                        | DIN-A   |
|           | 16K1A1417                                                           | 4       |
| part no:  | SEE TABLE                                                           |         |
|           |                                                                     | sh: 1/1 |

4

3

2

1