

06.84.356

**Locking Circuit Board Support /
Threaded Female**

Length 35,0 mm

Material Nylon 66

Thread Typ M4

Dia. Hole Board 4,0 mm

Dia. Hole Chassis 4,2 mm

Typ Support Threaded Male

UL-Flamability UL94 HB

Board Thickness 1,80 mm

Model Support Treaded Female

Colour black

Design Look / Thread

RoHS konform / WEEE konform / 76/769/EWG konform / PAKs frei

