

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC—

DIST—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	ECO-14-008835	26JUN14	AP	DM

NOTE:

1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND

2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO
TE-SPEC.108-18857, SUBSECTION 3.1.1

3. ASSEMBLY COLOR: WHITE

4. KEYING: HV-4

PN	L	TOLERANCES/mm
X-2083072-1	610mm (2ft)	+/- 5
X-2083072-2	1270mm (4ft)	+/- 15
X-2083072-3	1880mm (6ft)	+/- 20
X-2083072-4	2490mm (8ft)	+/- 20
X-2083072-5	3100mm (10ft)	+/- 30
X-2083072-6	3660mm (12ft)	+/- 30
X-2083072-7	4270mm (14ft)	+/- 50
X-2083072-8	4880mm (16ft)	+/- 50

VIEW A

+

-

1

2

3

6

VIEW B

-

+

3

4

5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
RAVINDRA K
28MAR11

CHK
R.HOSSAINI
31MAR11

APVD
R.HOSSAINI
31MAR11

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

TE Connectivity

CABLE ASSEMBLY NECTOR S LINE 2POS. HV-4,
MALE TO FEMALE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2083072

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
D

mm

AR

Cable SVT 2xAWG18 UL WH

6

PC

1

PLUG MINI HVL HV-4

5

PC

2

MICRO QUADLOK SYSTEM SOCKET CONTACT

4

PC

2

TUBE FOR SVT CABLE

3

PC

2

MICRO QUADLOK SYSTEM PIN CONTACT

2

PC

1

OUTLET, MINI HVL 7.5mm HV-4

1

UOM

QTY

DESCRIPTION

POS.

1

--X

1470-19 (3/11)