


[Search](#)
[Home](#)[Products](#)[Support](#)[Services](#)[Selectors](#)[How to Buy](#)

Rack PDU, Basic, 1U, 30A, 208V, (12) C13

APC Basic Rack PDU , Input: 208V , Input Connections: NEMA L6-30P , Cord Length: 12 feet (3.66 meters) , Output: 208V , Output Connections: IEC 320 C13

Includes: Installation Guide, Rack Mounting Brackets, User Manual

Part Number : **AP9571**


[Compare Models](#)

[Email Technical Specifications](#)

[Printer Friendly](#)

Additional Information

[Product Overview](#)
[User Manual & Installation Guides](#)
[Product Distribution](#)

[\[+\] More Images](#)

Technical Specifications

Output

Nominal Output Voltage	208V
Maximum Total Current Draw per Phase	24A

Output Connections	(12) IEC 320 C13
--------------------	------------------



Always on Outlets	12
Overload Protection	Yes

Input

Nominal Input Voltage	208V
Input Frequency	50/60 Hz
Regulatory Derated Input Current	24A

Input Connections	NEMA L6-30P
-------------------	-------------



Cord Length	12 feet (3.66 meters)
Acceptable Input Voltage	200-240 VAC
Maximum Line Current per phase	30A
Maximum Input Current per phase	30A
Load Capacity	4992 VA

Physical

Options:

- [AC Connections](#)

Features:

- Rack-Mountable
- Single-branch power input

Net Weight	5.60 lbs. (2.55 kg)
Maximum Height	1.70 inches (43 mm)
Maximum Width	17.50 inches (445 mm)
Maximum depth	2.50 inches (64 mm)
Shipping Weight	8.00 lbs. (3.64 kg)
Shipping Height	6.00 inches (152 mm)
Shipping Width	19.12 inches (486 mm)
Shipping Depth	6.95 inches (177 mm)
Color	Black

 Environmental

Operating Environment	-15 - 45 °C (5 - 113 °F)
Operating Relative Humidity	5 - 95%
Operating Elevation	0-15000 feet (0-4500 meters)
Storage Temperature	-25 - 65 °C (-13 - 149 °F)
Storage Relative Humidity	5 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

 Conformance

Regulatory Approvals	cUL Listed,UL 60950,UL Listed
Standard Warranty	2 years repair or replace

[Copyright](#) © American Power Conversion Corp., all rights reserved

[About APC](#)[Investors](#)[Job Seekers](#)[Press](#)[Feedback](#)[Contact](#)[Privacy Policy](#)