




ARRANGEMENT OF CONTACTS								SPECIFICATIONS	
PARTS	B2002-3P	B2002-4P	B2002-5P	B2002-5A	B2002-6P	B2002-7P	B2002-8P	Dielectric strength	1,000V AC/1 Minute
ANGLE	180°	216°	180°	240°	240°	270°	270°	Contact resistance	20M Ω Max.
POSITION OF VIEWS								Insulation resistance	100M Ω Min. at 500V DC
								Rating	100V AC 2A



4	GROUNDING	1	BSR-H (0.2t)	[C2680R]	SILVER PLATED	3-5U"
3	CONTACT TERMINAL	3	BSR-H (0.2t)	[C1519R-H]	SILVER PLATED	3-5U"
2	PLASTIC CORE	1	ABS	[777D]	BLACK	HB
1	METAL BODY	1	DIECAST		NICKEL	3-5U"
P/N	PART NAME	Q'TY	MATERIAL		PLATING	REMARKS

DRAWN	KIDD	APP'D		UNIT	MM	TOLERANCE			TITLE	B2002-3P METAL DIN CIRCULAR SOCKET			SHEET
CHK'D				SCALE	1:1	X ±0.20 XX ±0.10 XXX ±0.05 XXXX ±0.03 ANGULA ±1°			PART NO.	B2002-3P	DWG NO.	METAL DIN	VERSION
												A	