

Product Families

- > [Automation](#)
- > [Sensing](#)
- > [LED Lighting & Signaling](#)
- > [Machine Safety](#)
- > [Industrial Components](#)
 - > [Pushbuttons & Pilot Devices](#)
 - > [L6 Series](#)
 - > [HW Series](#)
 - > [XA Series](#)
 - > [XW Series](#)
 - > [TWTD Series](#)
 - > [A8 Series](#)
 - > [AP Series](#)
 - > [A6 Series](#)
 - > [LW Silhouette Series](#)
 - > [LW Series](#)
 - > [TW Series](#)
 - > [XN Series](#)
 - > [CS CAM Switch Series](#)
 - > [ARN Series](#)
 - > [FB Series](#)
 - > [E-Stop Stations](#)
 - > [Circuit Breakers](#)
 - > [Power Supplies](#)
 - > [Relays And Sockets](#)
 - > [Solid State Relays](#)
 - > [Timers](#)
 - > [IEC Contactors](#)
 - > [Terminal Blocks](#)

ASW33K22 22mm Key Switch 3 Position



MSRP: ****

[Add to Cart](#)

Key Features

- Corrosion resistant octagonal chrome plated locking bezel
- Snap on 10A contacts
- Modular construction for maximum flexibility
- NEMA 4X and IP65 watertight/oiltight panel sealing
- Available assembled or as sub-components
- UL Listed, CSA Certified, TUV Approved, and CE Marked



Specifications

Literature

Downloads

Product Type	Key Switch
Operation Type	Spring Return from Left and Right to Center
Mounting Hole Size	Ø22mm
Normally Open Contacts	2
Normally Closed Contacts	2
Shape	Round
Number of Positions	3
Key Removal	Key Retained in Left and Right (3-Position only)