




1P - 1T



示意图 SCHEMATIC

规格 Specifications

额定负荷 Ratings	DC 16 V 0.1 A
初期接触电阻 Initial Contact Resistance	40 mΩ Max.
绝缘电阻 Insulation Resistance	DC 250V 60 Sec. 100 MΩ Min.
抗电强度 Dielectric	AC 250 V (50~60HZ) 60 Sec.

操作力 Operating Force (gf)	30±15 gf
负荷寿命 Operating Life With Load	20,000 次 Cycles

5	端子B TERMINAL B	C5210R (a)	1	Ag CLAD				
4	端子A TERMINAL A	C5210R (a)	1	Ag CLAD	A01	增加规格栏见 (a)	曹文斌	06-03-27
3	杠杆 LEVER	POM	1	NATURAL		材料C5210R-EH变更为C5210R标示见 (a)		
2	胶壳 CASE	PBT	1	NATURAL	01		赖立辉	29 JUN 00
1	胶盖 COVER	PC	1	NATURAL	标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
序NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS	DWG NO. ITEM1803			

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	DETECTOR SWITCH		ITEM NO	DS-040-02		
UNDER 1	± 0.10	DRAWN	曹文斌	06-03-27	VERSION	A01	PAGE 1	OF 1
1 - 10	± 0.30	REVIEWED	张念明	06-03-27	SCALE		UNIT	mm
OVER 10	± 0.50	APPROVED	高洪	06-03-27	PROJECTION			

COMAX ELECTRONICS (HUIZHOU) CO.,LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Components:](#)

[DS-040-02](#)