


NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: XRCOLOR
HOUSING & PLUNGER: MOLDED NYLON TYPE 6,6.
AVAILABLE IN TEN COLORS.
CONTACT BLADE: BERYLLIUM COPPER PER QQ-C-533. GOLD PLATED PER MIL-G-45204 B TYPE 1 0.00001 [0.000254] THICK MINIMUM.
SPRING: STAINLESS STEEL TYPE 302.

2. P/N: W-600/COLOR
18AWG 65X36 TINNED COPPER
0.144 [3.66] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

3. PERFORMANCE
MAXIMUM CURRENT: 4.0 AMPS
MAXIMUM VOLTAGE: 5000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES		CONTRACT NO.		DESCRIPTION	
		±	.XX ±	±	APPROVALS	DATE	EZ-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A. MINI-HOOK (XR) JUMPER
			.XXX ±		DRAWN	R.L. 10/10	
		MATERIAL SEE NOTE.			APPROVED BY		
		FINISH SEE NOTE.					
NEXT ASSY	USED ON						SIZE CODE IDENT NO. DRAWING NO. REV.
APPLICATION	DO NOT SCALE DRAWING						A 08505 604XR
							SCALE 1:1 SHEET 1 OF 1