


.375 [9.53] HEX



.060 [1.52] MAX.
POTTING HEIGHT, 2 PL.

.250
[6.35]

.562±.031
[14.28]

.437
[11.10]

.750±.031
[19.05]

5/16-32UNEF-2A

#15 AWG.(Ø.057)

NOTES:

1. SUGGESTED MTG HOLE .328 DIA.
2. HARDWARE IS INCLUDED AND MUST BE PACKED IN THE SAME BAG QUANTITIES AS THE PART BAG QUANTITIES IN A GIVEN SHIPMENT.
3. MAXIMUM MOUNTING TORQUE=7LBS-IN
PRE FLATTEN/NOTCH DIMENSIONS, TOP-.542±.010,
BOTTOM-.730±.011

LEAD FINISH: SOLDER

BUSHING FINISH: SILVER

CAPACITANCE 3000 pF MIN.

TEMP. RANGE -55°C/ + 125°C

CURRENT 25 AMP MAX.

WORKING VOLTAGE 125°C 125VAC/400Hz
125°C 500 VDC MAX.

D.C. RESISTANCE .01ohms MAX.

MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD

FREQ. MHz I.L. (db)

1 ---


10 10

100 55

1 GHz 70

10 GHz 70

SCHEMATIC



MARKING:

PART: S1202054

BAG: 1202-054
XXXX DATE CODE
XXX QTY./BAG
(50/ BAG MAX.)

6

5

4

3

REV.
NO.

TOLERANCES UNLESS
OTHERWISE SPECIFIED

Fractions ± 1/64

Dec. .xx±

Dec. .xxx± .010

Angles ±0° 30'

CODE IDENT. NO.
DLSP2

CHANGE NOTICE

CN #15200

CN 68302-ENG

CN 205223

REDRAWN

CN 185001

REDRAWN

api
technologies corp.

FAIRVIEW
PENNSYLVANIA

Dwn. KRDZALIC

Ckd. 8-17-15

Apvd.

Scale NONE

Description

FLTR., SING., Pi, BSHG.

1202-054