

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19

BY -

ALL RIGHTS RESERVED.

LOC
DYDIST
-

REVISIONS





P	LTR	DESCRIPTION	DATE	DWN	APVD
	J2	REVISED PER ECO-11-005139	19MAR11	RK	HMR

NOTES:

1 MATERIAL:
HOUSING: GLASS FILLED HIGH TEMP NYLON, NATURAL COLOR (BEIGE)
CONTACT: PHOSPHOR BRONZE



2 FINISH: MATTE TIN OVER NICKEL UNDERPLATE

3. PACKAGING: TAPE & REEL (PACKAGING SPEC: 107-51189)



SECTION B-B
(FOR ODD POSITION CONTACTS)
SCALE 10:1

RECOMMENDED PCB LAYOUT
(FOR ODD POSITION CONNECTORS)



RECOMMENDED PCB LAYOUT
(NON-ACCUMULATIVE TOLERANCE)
(FOR EVEN POSITION CONNECTORS)

29.00	32.00	31.00	31.00	30	3-84982-0
28.00	31.00	30.00	30.00	29	2- -9
27.00	30.00	29.00	29.00	28	2- -8
26.00	29.00	28.00	28.00	27	2- -7
25.00	28.00	27.00	27.00	26	2- -6
24.00	27.00	26.00	26.00	25	2- -5
23.00	26.00	25.00	25.00	24	2- -4
22.00	25.00	24.00	24.00	23	2- -3
21.00	24.00	23.00	23.00	22	2- -2
20.00	23.00	22.00	22.00	21	2- -1
19.00	22.00	21.00	21.00	20	2-84982-0
18.00	21.00	20.00	20.00	19	1- -9
17.00	20.00	19.00	19.00	18	1- -8
16.00	19.00	18.00	18.00	17	1- -7
15.00	18.00	17.00	17.00	16	1- -6
14.00	17.00	16.00	16.00	15	1- -5
13.00	16.00	15.00	15.00	14	1- -4
12.00	15.00	14.00	14.00	13	1- -3
11.00	14.00	13.00	13.00	12	1- -2
10.00	13.00	12.00	12.00	11	1- -1
9.00	12.00	11.00	11.00	10	1-84982-0
8.00	11.00	10.00	10.00	9	-9
7.00	10.00	9.00	9.00	8	-8
6.00	9.00	8.00	8.00	7	-7
5.00	8.00	7.00	7.00	6	-6
4.00	7.00	6.00	6.00	5	-5
3.00	6.00	5.00	5.00	4	84982-4
H	G	F	E	POS.	PART NO.

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN WYLEE	19MAY2006
				CHK KTGOH	19MAY2006
				APVD SFLEONG	19MAY2006
				PRODUCT SPEC 108-51054	
				APPLICATION SPEC -	
				WEIGHT -	
MATERIAL		FINISH		CUSTOMER DRAWING	
1		2			



TE Connectivity

NAME ASSY, 1.00mm FFC CONN SMT, V, (NON-ZIF)			
SIZE A3	CAGE CODE 00779	DRAWING NO C-84982	
SCALE 5:1		SHEET 1	REV J2