

PRODUCT NUMBER

71600-YXXXLF

LEAD FREE, SEE NOTE 6

COLOR OPTION, SEE NOTE 1

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2

OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5

LEFT POLARIZING
NOTE 5

CENTRAL KEY
NOTE 5

RIGHT POLARIZING
NOTE 5

NOTES:

1 - HOUSING MATERIAL : GLASS FILLED
THERMOPLASTIC. UL94V-0 COLOR: GREY

= STANDARD COLOR GREY

B = OPTION COLOR BLACK

2 - PIN MATERIAL : PHOSPHOR BRONZE

3 - PRODUCT PACKAGED IN TUBES.

4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm

5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.

- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO
LEFT AND RIGHT POLARIZING SLOT.




- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT
POLARIZING SLOT.

- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT

- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT

6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS PER GS-22-008.

PACKAGING SPECIFICATION AS PER GS-14-920.




D-D SECTION


mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection mm		product family 2.54MM IDC	
lfr	ecn	no	dr	date	tolerances unless otherwise specified			mm		title	
AP	F12-0046	LMU		12.04.25	angles		X.X ±0.3			QUICKIE III FEM	
AR	B-17851	LMU		14.06.05	linear		X.XX ±0.13			0.76µm Au	
AS	F-26816	LMU		17.06.06			X.XXX ±0.05	scale 5:1		dwg no	
AL	F06-0270	LMU		06.09.12	dr	D.LE	01.01.24			sheet 1 of 2 size	
AM	F06-0274	LMU		06.09.25	enrg	P.NZ	01.01.24			71600	
AN	F09-0233	LMU		09.12.15	chr	JF.N	01.01.24			A3	
sheet	revision	AS	AG		appd	P.NZ	01.01.24			type	
index	sheet	1	2							CUSTOMER Drawing	

STRAIN RELIEF OPTION AVAILABILITY	Nbr OF POSITIONS
1/6	04
0/1/2/3/6	06
0/1/2/3/6	08
0/1/2/3/6	10
0/1/2/3/6	14
0/1/2/3/6	16
0/1/2/3/6	18
0/1/2/3/6	20
0/1/3	24
0/1/2/3/6	26
0/1/2/3/6	30
0/1/2/3/6	34
0/1/2/3/6	40
0/1/2/3/6	50
0/1/2/3/6	60
0/1/2/3/6	64
PLATING 0.76µm GOLD ON CONTACT AREA 1.27 µm Ni REMAINDER OF PRODUCT	


624
304
204 / 224
004
DASHES NOT AVAILABLE




WITHOUT STRAIN RELIEF




WITH LOW PROFILE STRAIN RELIEF




WITH STANDARD STRAIN RELIEF




WITH LATCHING STRAIN RELIEF



LOW PROFILE
STRAIN RELIEF



STANDARD
STRAIN RELIEF



LATCHING STRAIN RELIEF
FOR SLIM HEADER

71600-6YY(B)LF	●					●
71600-3YY(B)LF		●	●			
71600-2YY(B)LF	●				●	
71600-1YY(B)LF	●			●		
71600-0YY(B)LF	●		●			
PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING
			STRAIN RELIEF			

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
AF	B-17851	LMU	14.06.05	angles	linear					IDC RECEPT DR			
AG	F-26816	LMU	17.06.06					scale N/A					
AB	F03019	DLE	03.01.23	dr	D.LE	01.01.24				dwg no		sheet 2 of -	size
AC	F05-0180	LMU	05.04.22	engr	P.NZ	01.01.24				71600		A3	
AD	F06-0270	LMU	06.09.12	chr	JF.N	01.01.24							
AE	F06-0274	LMU	06.09.25	appd	P.NZ	01.01.24							
sheet index	revision		sheet										

