



**Series CE/CT  
Connectors .100"**

**.100" (2.54 mm) End and  
Through Connectors  
Available in 2-28 Circuits  
with Optional Cover**



**Dimensions**



**Snap-on Covers EC**

**Snap-on Covers TC**



**Strain Relief Combination Cover SCC**



**Dimensions - Dual Dims**

| No. of Circuits       | 2 | 3              | 4              | 5               | 6               | 7               | 8               | 9               | 10              | 11               | 12               | 13               | 14               | 15               | 16               | 17               | 18               | 19               | 20               | 21               | 22               | 23               | 24               | 25               | 26               | 27               | 28               |                  |
|-----------------------|---|----------------|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|-----------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|------------------|
| Dim. in<br>in. / (mm) | a | .200<br>(5.08) | .300<br>(7.62) | .400<br>(10.16) | .500<br>(12.70) | .600<br>(15.24) | .700<br>(17.78) | .800<br>(20.32) | .900<br>(22.86) | 1.000<br>(25.40) | 1.100<br>(27.94) | 1.200<br>(30.48) | 1.300<br>(33.02) | 1.400<br>(35.56) | 1.500<br>(38.10) | 1.600<br>(40.64) | 1.700<br>(43.18) | 1.800<br>(45.72) | 1.900<br>(48.25) | 2.000<br>(50.80) | 2.100<br>(53.34) | 2.200<br>(55.88) | 2.300<br>(58.42) | 2.400<br>(60.96) | 2.500<br>(63.50) | 2.600<br>(66.04) | 2.700<br>(68.58) | 2.800<br>(71.12) |
|                       | b | .100<br>(2.54) | .200<br>(5.08) | .300<br>(7.62)  | .400<br>(10.16) | .500<br>(12.70) | .600<br>(15.24) | .700<br>(17.78) | .800<br>(20.32) | .900<br>(22.86)  | 1.000<br>(25.40) | 1.100<br>(27.94) | 1.200<br>(30.48) | 1.300<br>(33.02) | 1.400<br>(35.56) | 1.500<br>(38.10) | 1.600<br>(40.64) | 1.700<br>(43.18) | 1.800<br>(45.72) | 1.900<br>(48.25) | 2.000<br>(50.80) | 2.100<br>(53.34) | 2.200<br>(55.88) | 2.300<br>(58.42) | 2.400<br>(60.96) | 2.500<br>(63.50) | 2.600<br>(66.04) | 2.700<br>(68.58) |

No. of Circuits 2-28 \*(Contact Factory For Circuit Availability)

□□ = Number of Circuits

| Version                  | Wire Size    |              |              |              | Dimension     |
|--------------------------|--------------|--------------|--------------|--------------|---------------|
|                          | AWG 28       | AWG 26       | AWG 24       | AWG 22       | c inches (mm) |
| End Connector            | CE100F28- □□ | CE100F26- □□ | CE100F24- □□ | CE100F22- □□ | .27 (6.9)     |
| Through Connector        | CT100F28- □□ | CT100F26- □□ | CT100F24- □□ | CT100F22- □□ | .30 (7.6)     |
| AWG Identification Color | Green        | Blue         | Black        | Red          |               |

|                                      |            |
|--------------------------------------|------------|
| Snap-on Cover for End connectors     | EC 100F-□□ |
| Snap-on Cover for Through connectors | TC 100F-□□ |
| Strain Relief Combination Cover      | SCC100F-□□ |