

PRODUCT SPECIFICATION



Brand	C.K
Product Range	TiN coated screwdriver bits
Catalogue number	4551, 4552, 4555, 4556, 4557, 4561, 4562, 4579 & 4580
Date	21/10/2008

Range Description

A range of professional quality TiN coated Chrome Vanadium screwdriver bits

Features

- Chrome vanadium steel
- TiN coated for high wear resistance
- Precision machined
- Grip Tip anti cam out ribs positively engage with the screw head to reduce the risk of slip and cam out on * marked items

featuring **GRIP TIP**[®] technology
ON SELECTED SIZES



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4551TIN 1	Screwdriver Bit PH1 TIN Loose*		82079030	300
T4551TIN 2	Screwdriver Bit PH2 TIN Loose*		82079030	300
T4551TIN 3	Screwdriver Bit PH3 TIN Loose*		82079030	300
T4552TIN 1	Screwdriver Bit PZD/SDV 1 TIN Loose*		82079030	300
T4552TIN 2	Screwdriver Bit PZD/SDV 2 TIN Loose*		82079030	300
T4552TIN 3	Screwdriver Bit PZD/SDV 3 TIN Loose*		82079030	300
T4555TIN 1T	Screwdriver Bit PH1x50mm TIN Card/2*	5013969703382	82079030	20
T4555TIN 2T	Screwdriver Bit PH2x50mm TIN Card/2*	5013969703399	82079030	20
T4556TIN 1	Screwdriver Bit PZD1x50mm TIN Loose*		82079030	300
T4556TIN 2	Screwdriver Bit PZD2x50mm TIN Loose*		82079030	300
T4556TIN-1T	Screwdriver Bit PZD1x50mm TIN Card/2*	5013969703634	82079030	20
T4556TIN-2T	Screwdriver Bit PZD2x50mm TIN Card/2*	5013969703641	82079030	20
T4557TIN 10	Screwdriver Bit TX10 TIN Loose		82079030	300
T4557TIN 15	Screwdriver Bit TX15 TIN Loose		82079030	300
T4557TIN 20	Screwdriver Bit TX20 TIN Loose		82079030	300
T4557TIN 25	Screwdriver Bit TX25 TIN Loose		82079030	300
T4557TIN 30	Screwdriver Bit TX30 TIN Loose		82079030	300
T4557TIN 40	Screwdriver Bit TX40 TIN Loose		82079030	300
T4557TIN-10T	Screwdriver Bit TX10 TIN Card/2		82079030	20
T4557TIN-15T	Screwdriver Bit TX15 TIN Card/2		82079030	20
T4557TIN-20T	Screwdriver Bit TX20 TIN Card/2	5013969702668	82079030	20
T4557TIN-25T	Screwdriver Bit TX25 TIN Card/2	5013969702675	82079030	20
T4557TIN-30T	Screwdriver Bit TX30 TIN Card/2	5013969702682	82079030	20
T4557TIN-40T	Screwdriver Bit TX40 TIN Card/2	5013969702699	82079030	20
T4561TIN 1	Screwdriver Bit PH 1 TIN Card/2*	5013969975130	82079030	20
T4561TIN 2	Screwdriver Bit PH 2 TIN Card/2*	5013969975147	82079030	20
T4561TIN 3	Screwdriver Bit PH 3 TIN Card/2*	5013969975154	82079030	20
T4562TIN 1	Screwdriver Bit PZD 1 TIN Card/2*	5013969027594	82079030	20
T4562TIN 2	Screwdriver Bit PZD 2 TIN Card/2*	5013969027600	82079030	20
T4562TIN 3	Screwdriver Bit PZD 3 TIN Card/2*	5013969027617	82079030	20
T4562TIN-215	Screwdriver Bit PZD2 TIN Box /15*	5013969702750	82079030	60
T4562TIN-2CB	Screwdriver Bit PZD2 Counter Box of 12xT4562TIN-215*	5013969702767	82079030	1
T4579TIN-1T	Screwdriver Bit PZD1xSlotted 4mm TIN Card/2*	5013969702798	82079030	20
T4579TIN-2T	Screwdriver Bit PZD2xSlotted 7mm TIN Card/2*	5013969702804	82079030	20
T4580TIN-1T	Screwdriver Bit PH1xSlotted 4mm TIN Card/2*	5013969703658	82079030	20
T4580TIN-2T	Screwdriver Bit PH2xSlotted 7mm TIN Card/2*	5013969703665	82079030	20

Technical product information	
Standards compliance	All 25mm Bits have DIN 3126-C6,3. ISO 1173 drive All 50mm single ended bits have DIN 3126-E6,3. ISO 1173 drive
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K screwdriver bits are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4551TIN 1	7	7	25	5	-	-	-	-
T4551TIN 2	7	7	25	5	-	-	-	-
T4551TIN 3	7	7	25	5	-	-	-	-
T4552TIN 1	7	7	25	5	-	-	-	-
T4552TIN 2	7	7	25	5	-	-	-	-
T4552TIN 3	7	7	25	5	-	-	-	-
T4555TIN 1T	7	7	50	11	48	7	125	25
T4555TIN 2T	7	7	50	11	48	7	125	25
T4556TIN 1	7	7	50	11	-	-	-	-
T4556TIN 2	7	7	50	11	-	-	-	-
T4556TIN-1T	7	7	50	11	48	7	125	25
T4556TIN-2T	7	7	50	11	48	7	125	25
T4557TIN 10	7	7	25	5	-	-	-	-
T4557TIN 15	7	7	25	5	-	-	-	-
T4557TIN 20	7	7	25	5	-	-	-	-
T4557TIN 25	7	7	25	5	-	-	-	-
T4557TIN 30	7	7	25	5	-	-	-	-
T4557TIN 40	7	7	25	5	-	-	-	-

T4557TIN-10T	7	7	25	5	48	7	125	12
T4557TIN-15T	7	7	25	5	48	7	125	12
T4557TIN-20T	7	7	25	5	48	7	125	12
T4557TIN-25T	7	7	25	5	48	7	125	12
T4557TIN-30T	7	7	25	5	48	7	125	13
T4557TIN-40T	7	7	25	5	48	7	125	15
T4561TIN 1	7	7	25	5	48	7	125	12
T4561TIN 2	7	7	25	5	48	7	125	13
T4561TIN 3	7	7	25	5	48	7	125	13
T4562TIN 1	7	7	25	5	48	7	125	12
T4562TIN 2	7	7	25	5	48	7	125	12
T4562TIN 3	7	7	25	5	48	7	125	13
T4562TIN-215	7	7	25	5	43	7	25	92
T4562TIN-2CB	7	7	25	5	43	7	25	92
T4579TIN-1T	7	7	50	11	48	7	125	21
T4579TIN-2T	7	7	50	11	48	7	125	24
T4580TIN-1T	7	7	50	11	48	7	125	21
T4580TIN-2T	7	7	50	11	48	7	125	24

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4551TIN 1	75	195	45	1365		
T4551TIN 2	75	195	45	1455		
T4551TIN 3	75	195	45	1515		
T4552TIN 1	75	195	45	1365		
T4552TIN 2	75	195	45	1455		
T4552TIN 3	75	195	45	1515		
T4555TIN 1T	75	195	45	548		
T4555TIN 2T	75	195	45	556		
T4556TIN 1	100	345	65	3445		

T4556TIN 2	100	345	65	3505		
T4556TIN-1T	75	195	45	548		
T4556TIN-2T	75	195	45	556		
T4557TIN 10	75	195	45	1305		
T4557TIN 15	75	195	45	1365		
T4557TIN 20	75	195	45	1395		
T4557TIN 25	75	195	45	1455		
T4557TIN 30	75	195	45	1635		
T4557TIN 40	75	195	45	1875		
T4557TIN-10T	75	195	45	280		
T4557TIN-15T	75	195	45	288		
T4557TIN-20T	75	195	45	292		
T4557TIN-25T	75	195	45	300		
T4557TIN-30T	75	195	45	324		
T4557TIN-40T	75	195	45	356		
T4561TIN 1	75	195	45	288		
T4561TIN 2	75	195	45	300,4		
T4561TIN 3	75	195	45	320,4		
T4562TIN 1	75	195	45	288		
T4562TIN 2	75	195	45	300		
T4562TIN 3	75	195	45	320		
T4562TIN-215	130	310	120	5710		
T4562TIN-2CB	170	125	75	1220		
T4579TIN-1T	75	195	45	478		
T4579TIN-2T	75	195	45	534		
T4580TIN-1T	75	195	45	478		
T4580TIN-2T	75	195	45	534		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4551TIN 1	1	Bag					48	Box
T4551TIN 2	1	Bag					48	Box
T4551TIN 3	1	Bag					48	Box
T4552TIN 1	1	Bag					48	Box
T4552TIN 2	1	Bag					48	Box

T4552TIN 3	1	Bag					48	Box
T4555TIN 1T	0.6	Blister	4	Backing card			48	Box
T4555TIN 2T	0.6	Blister	4	Backing card			48	Box
T4556TIN 1	1	Bag					48	Box
T4556TIN 2	1	Bag					48	Box
T4556TIN-1T	0.6	Blister	4	Backing card			48	Box
T4556TIN-2T	0.6	Blister	4	Backing card			48	Box
T4557TIN 10	1	Bag					48	Box
T4557TIN 15	1	Bag					48	Box
T4557TIN 20	1	Bag					48	Box
T4557TIN 25	1	Bag					48	Box
T4557TIN 30	1	Bag					48	Box
T4557TIN 40	1	Bag					48	Box
T4557TIN-10T	0.6	Blister	4	Backing card			48	Box
T4557TIN-15T	0.6	Blister	4	Backing card			48	Box
T4557TIN-20T	0.6	Blister	4	Backing card			48	Box
T4557TIN-25T	0.6	Blister	4	Backing card			48	Box
T4557TIN-30T	0.6	Blister	4	Backing card			48	Box
T4557TIN-40T	0.6	Blister	4	Backing card			48	Box
T4561TIN 1	0.6	Blister	4	Backing card			48	Box
T4561TIN 2	0.6	Blister	4	Backing card			48	Box
T4561TIN 3	0.6	Blister	4	Backing card			48	Box
T4562TIN 1	0.6	Blister	4	Backing card			48	Box
T4562TIN 2	0.6	Blister	4	Backing card			48	Box
T4562TIN 3	0.6	Blister	4	Backing card			48	Box
T4562TIN-215	0.6	Blister	4	Backing card			48	Box
T4562TIN-2CB					40	Shrink wrap & tray	86	Box
T4579TIN-1T	0.6	Blister	4	Backing card			48	Box
T4579TIN-2T	0.6	Blister	4	Backing card			48	Box
T4580TIN-1T	0.6	Blister	4	Backing card			48	Box
T4580TIN-2T	0.6	Blister	4	Backing card			48	Box