

6

5



4

3

2

1

MATERIAL NUMBER	OLD PART NUMBER
130057-0001	ENQAM315



VOLTAGE RATING	250 VAC/VDC
AMPERAGE RATING	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT HOUSING	POLYCARBONATE	CLEAR
2	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
3	COUPLING NUT	ABS	BLACK
4	O-RING	VITON	BLACK
5	HOUSING	ABS	BLACK

RLSD DRAWING
EC NO: WNA209-0659
DRWN: BWOODMAN
CHKD: JM
APPR: JFMURPHY
2009/04/17

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±.01
1 PLACE	±0.3	±---

ANGULAR ±---°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY DATE
BW 2009/04/03
CHECKED BY DATE
TW 2009/04/03
APPROVED BY DATE

SCALE

DESIGN UNITS

THIRD ANGLE
PROJECTION

TITLE
RJ-LNXX ATTACHABLE
FOR STRANDED CABLE

MOLEX INCORPORATED

MATERIAL NO.
SEE CHART

DOCUMENT NO.
SD-130057-001

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

6

5

4

3

2

1