

Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Blue, 2-ft.

MODEL NUMBER: **N201-002-BL**



Description

With Tripp Lite's new Category 6 snagless molded patch cables you can stay ahead of the game by distributing data, voice and video at higher speeds. These cables deliver stable performance up to 550MHz. Each comes UL verified and meets EIA/TIA Cat6 TIA/EIA-568-B-2.1 draft 9 standards. Constructed with high-quality copper wire and a staggered-pin plug design, near-end crosstalk levels are kept to a minimum. Designed for use in Category 6, Category 5e and Category 5 applications. Cat6 cables are available in a variety of colors with a snagless boot preventing cable snags.

Features

- Premium cabling for category 6, category 5e and category 5 applications
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- Length: 2-ft./Color: blue/Connectors: RJ45 male
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- PVC 4-pair stranded UTP
- Deliver stable performance up to 550MHz/1 Gbps

Specifications

| OVERVIEW | |
|----------------------|----------------------|
| Intended Application | Computer Networking |
| Cable Type | CAT6 / CAT6E / CAT6A |

Highlights

- Premium cabling for Category 6, Category 5e and Category 5 applications, rated for 550 MHz/1 Gbps communications
- Designed to meet Category 6 specifications; reduces cross-talk and return loss
- IEC 802.3ab
- PVC 4-pair stranded UTP
- Features boots with integral strain-relief and RJ45 (Male) connectors

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

Package Includes

- 2-ft. Cat6 Gigabit Blue Snagless Molded Patch Cable

| | |
|-------------------------------------|--|
| Model Type | Snagless Patch Cables |
| INPUT | |
| Cable Length (ft.) | 2 |
| Cable Length (m) | 0.61 |
| UPC ASSIGNMENT | |
| Unit Carton UPC# | 037332116437 |
| PHYSICAL | |
| Color | Blue |
| Style | Cat6/6e/6a |
| CONNECTIONS | |
| Connector A |  RJ45 (MALE) |
| Connector B |  RJ45 (MALE) |
| Number of Connectors | 2 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

Related Items

Optional Products

| Model Number | Description | Qty. |
|-----------------------------|---|------|
| N201-003-BK | 3-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Black | 1 |
| N201-003-GY | 3-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray | 1 |
| N201-005-GY | 5-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray | 1 |
| N201-007-GY | 7-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray | 1 |
| N201-010-GY | 10-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray | 1 |
| N201-014-GY | 14-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray | 1 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

N201-025-GY

25-ft. Cat6 Gigabit Snagless Molded Patch Cable
(RJ45 M/M) - Gray

1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:
<http://www.tripplite.com/sku/N201-002-BL>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.