

[Home](#)> [5973007607F](#)

Search For

Part Number



Part Number: **5973007607F**

General Description	
Series	597
Configuration	1206 Package
Description	SMD LED 1206 7" Reel
Package Options	Tape and Reel
Lamp Type	Single Color
Lens Color	Non - Diffused

Absolute Maximum Ratings (Ta = 25Â°)	
Forward Current mA	30mA
Reverse Current	100 @ Vr =5V
Forward Current Pulsed	120mA
Derating	from 50Â° @ .6mA/Â°C
Solder Temperature	260Â° for 5 sec
Operating Temperature	-55 - + 85
Storage Temperature	-55 - + 85

Operating Characteristics	
Color	Red
Luminous Intensity Min	4
Luminous Intensity Typical	8
Luminous Intensity Max	30
Test Current mA	20mA
Dominant Wavelength Typical	621nm
Power Dissipation Max	100mW



 [597 -3xxx -4xx Datasheet](#)

5973007607F

check stock 



[This is a
RoHS Compliant Product](#)
[To learn more click here](#)