



Sample photo

Order symbol: PC 200/63 HG
Product nbr: 6011324
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074051912
El. number:
 Finland 3435264
 Denmark 8212022250

Including: Base with TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:		L	W	H	Rating:
mm:		255	180	63	Ingress Protection (EN 60529): IP 66/67
inch:		10	7.1	2.5	Impact Resistance (EN 50102): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		PC			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Gasket material:		TPE			Certificates:
Temperatures:					Germanischer Lloyd (GL)
Short term:		-40 ... 120 °C			Underwriters Laboratories
Continuous:		-40 ... 80 °C			Det Norske Veritas
Short term:		-40 ... 250 °F			Fimko
Continuous:		-40 ... 175 °F			Europe EN 50298 1998
Accessories:					UL Canada
MIV 200		Mounting plate			Gost R
MIN 15		DIN-15 Mounting rail			
MIN 20		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
MIV 20		DIN-35 Mounting rail			
FP A 200/180		Front plate			
HFP 180		Front plate hinge series			

