

Wiha TORXPlus® Insert Bits and Power Bits

TORXPlus®

Made in Germany -
Production Quality

High resistant
to wear and
tear for a
long tool life

Impact resistant modified
chrome-vanadium-molybdenum,
tool steel, hardened

Suitable for all applications
Hardness HRC 59-61
Suitable for both manual and
machine applications



SHOP

716 TORXPlus® Insert Bits, 1/4" Hex, 1" OAL

Item No.	Size	mm	pkg.	lbs.
716 03	IP3	25	10	.12
716 04	IP4	25	10	.12
716 05	IP5	25	10	.12
716 06	IP6	25	10	.12
716 07	IP7	25	10	.12
716 08	IP8	25	10	.12
716 09	IP9	25	10	.12
716 10	IP10	25	10	.12
716 15	IP15	25	10	.12
716 20	IP20	25	10	.12
716 25	IP25	25	10	.12
716 27	IP27	25	10	.13
716 30	IP30	25	10	.13
716 40	IP40	25	10	.15



SHOP

746 TORXPlus® Power Bits, 1/4" Hex, 2" OAL

Item No.	Size	mm	pkg.	lbs.
746 02	IP6	50	10	.18
746 03	IP7	50	10	.18
746 04	IP8	50	10	.18
746 08	IP9	50	10	.18
746 12	IP10	50	10	.20
746 16	IP15	50	10	.20
746 20	IP20	50	10	.20
746 24	IP25	50	10	.20
746 28	IP27	50	10	.25
746 32	IP30	50	10	.25
746 36	IP40	50	10	.25



SHOP

716 TORXPlus® Insert Bit Packs, 1"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.	2 Bit Pack
716 31	IP3	25	.03	
716 32	IP4	25	.03	
716 33	IP5	25	.03	
716 34	IP6	25	.03	
716 35	IP7	25	.03	
716 36	IP8	25	.03	
716 37	IP9	25	.03	
716 38	IP10	25	.03	
716 39	IP15	25	.03	
716 41	IP20	25	.03	
716 42	IP25	25	.03	
716 43	IP27	25	.03	
716 44	IP30	25	.03	
716 45	IP40	25	.04	

SHOP

746 TorxPlus® Power Bit Packs, 2"

Item No.	Size	mm	lbs.	2 Bit Pack
746 60	IP6	50	.05	
746 61	IP7	50	.05	
746 62	IP8	50	.05	
746 63	IP9	50	.05	
746 64	IP10	50	.05	
746 65	IP15	50	.05	
746 66	IP20	50	.05	
746 67	IP25	50	.05	
746 68	IP27	50	.05	
746 69	IP30	50	.05	
746 70	IP40	50	.05	



Wiha Ball End TORX® Bits

NEW
From Wiha

SHOP

745 Ball End TORX® Bits. 1/4" Hex Drive,
Length 2.0"/50mm

Item No.	Size	mm	pkg.	lbs.
745 24	T9	50	10	.18
745 26	T10	50	10	.18
745 28	T15	50	10	.18
745 32	T20	50	10	.18
745 34	T25	50	10	.18
745 37	T27	50	10	.18
745 39	T30	50	10	.18
745 41	T40	50	10	.18

NEW
From Wiha

SHOP

745 Ball End TORX® Power Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.	2 Bit Pack
745 05	T9	50	.05	
745 20	T10	50	.05	
745 22	T15	50	.05	
745 43	T20	50	.05	
745 45	T25	50	.06	
745 47	T27	50	.06	
745 49	T30	50	.08	
745 50	T40	50	.08	

Wiha Bit Holders

Quick
Release714 ClickFix Bit Holder,
Magnetic For Insert Bits

Item No.	Size	Size	mm	Inch
714 90	1/4"	1/4"	60	2.4
714 91	1/4"	1/4"	75	2.9

Quick Release
SHOP

714 RapidFix Bit Holder For Power Bits

Item No.	Size	Size	mm	Inch
714 80	1/4"	1/4"	60	2.3