

HC-M-KV-M32(19-27)

Order No.: 1646010

The illustration shows version HC-M-KV-M20



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1646010>

Metal screw connection up to 5 bar, thread length: 8 mm, cable diameter: 19 - 27 mm, WAF 43, screw connection: M32

Commercial data

GTIN (EAN)	4 017918 941253
sales group	D092
Pack	10 pcs.
Customs tariff	74199990
Catalog page information	Page 521 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
06/13/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Cable gland material	Nickel-plated brass
Seal material	Neoprene
Cable seal material	Neoprene
Material, O-ring	NBR
Wrench size, union nut	34 mm

Wrench size, support	34 mm
Thread type connection side 1	M32
Length of the connecting thread	8.00 mm
External cable diameter	19 mm ... 27 mm
Conductor sealing range	19.00 mm ... 27.00 mm
Tightening torque, union nut	15.00 Nm
Degree of protection	IP68, to 5 bar
Ambient temperature (operation)	-20 °C ... 100 °C

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;