


Number of contacts

15–78



High density with stamped solder pins, angled with grounding board locks

Identification	No. of contacts	Part No.			
Performance levels Explanations see page 05.04 Other performance levels on request		Performance level 3		S4 ¹⁾	
Male connector metal shell with dimples					
	15	09 56 162 781 .		09 56 162 581 .	
	26	09 56 262 781 .		09 56 262 581 .	
	44	09 56 362 781 .		09 56 362 581 .	
	62	09 56 462 781 .		09 56 462 581 .	
Female connector metal shell					
	15	09 56 152 761 .		09 56 152 561 .	
	26	09 56 252 761 .		09 56 252 561 .	
	44	09 56 352 761 .		09 56 352 561 .	
	62	09 56 452 761 .		09 56 452 561 .	
	78	09 56 552 761 .		09 56 552 561 .	
Please insert digit for flange thread or fitted female screw locks					
4-40 UNC ► 2					
fitted screw locks 4-40 UNC ► 3					

¹⁾ S4: ≥ 0.76 µm Au (30 µinch)