

WCY49

BURNDY® PRODUCTS

WCY49

WCY49 : WEJTAP CONN YEL



ACTIVE

RoHS
compatible[Assistant](#)[Add to Favorites](#)[Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)[Sample request](#)[Price request](#)

Specifications

[Download document](#)

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)	0.537 to 0.75		
Conductor Size (Run - mm)	14 mm² to 19 mm²		
Conductor Size (Run)	3975		
Conductor Size (Tap)	#4		
Conductor Type (Run)	AAC		
Wire Size	AWG		
Wire Size (Tap - Diameter - in)	0.203 to 0.271		
Wire Size (Tap - mm)	5 mm² to 7 mm²		
Wire Type (Tap)	AAC Copper		
Physical			
Color Code	Yellow		
Approvals / Certifications			
UL Listed	No		
CSA Certified	No		
Other Features			
Installation Tool	WTRB		
Booster	WPBY Box 25		
UPC	78181087385		
Keyword	w ejtap		