


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [502598-4591](#)
Status: **Active**
Description: 0.30mm Pitch Easy-On™ BackFlip™ FPC Connector, Right Angle, SMT,Dual Contact Style, 1.15mm Mated Height, 45 Circuits

Documents:

- [3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-502598-001 \(PDF\)](#)
[Product Specification PS-502598-002 \(PDF\)](#)
- [Application Specification AS-502598-001 \(PDF\)](#)
[Packaging Specification SPK-502598-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)



General

Product Family	FFC/FPC Connectors
Series	502598
Product Name	BackFlip™, Easy-On™

Physical

Circuits (Loaded)	45
Color - Resin	Black, White
Contact Position	Dual
Durability (mating cycles max)	10
Entry Angle	90° Angle
Mated Height	1.15mm
Material - Metal	Copper Alloy, Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold, Tin
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount
Wire/Cable Type	FPC only

Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Net Weight	108.887/mg
UPC	800756671703

Reference - Drawing Numbers

Application Specification	AS-502598-001
Packaging Specification	SPK-502598-001
Product Specification	PS-502598-001, PS-502598-002, RPS-502598-001, RPS-502598-005, RPS-502598-009, RPS-502598-010
Sales Drawing	SD-502598-001, SD-502598-002

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[502598Series](#)