

- RC-12P1N8AB1EN - 1597575

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Feed-through of front wall, straight, shielded: Yes, Screw locking, M23, Number of positions: 12, Type of contact: Male connector, Crimp connection, Flat gasket, 4xØ3,2, Panel thickness min.: 3 mm, Panel thickness max.: 7 mm, Cable diameter: 3 mm ... 10.5 mm

Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	74.41 GRM
Custom tariff number	85366990
Country of origin	Germany

Technical data

Product type	Circular connector (cable-side)
--------------	---------------------------------

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440103

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC001121

- RC-12P1N8AB1EN - 1597575

Classifications

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404